



Everyday™ Yellow Toner by Xerox compatible with Brother
TN225Y/ TN245Y, High capacity

Brand : Xerox Product family: Everyday Product code: 006R04229

Product name : Everyday™
Yellow Toner by Xerox
compatible with Brother TN225Y/
TN245Y, High capacity

Everyday™ Yellow Toner by Xerox compatible with Brother TN225Y/ TN245Y, High capacity

Everyday™ Yellow Toner by Xerox compatible with Brother TN225Y/ TN245Y, High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Yellow Toner by compatible with Brother TN225Y/ TN245Y, High capacity. Black toner page yield: 2200 pages, Colour toner page yield: 2200 pages, Printing colours: Yellow, Quantity per pack: 1 pc(s)



Cut Toner Costs, Not Quality

Save big with 40-60% savings on major printer brands.

Features		Features	
Compatibility *	DCP-9015 DCP-9020 HL-3140	Country of origin	China
	HL-3150 HL-3170 HL-3180	Packaging data	
	MFC-9130 MFC-9140 MFC-9330	Package dimensions (W x D x H)	110 x 320 x 110 mm (4.33 x 12.6 x 4.33")
	MFC-9340	Package weight (imperial)	0.626 kg (1.38 lbs)
Quantity per pack *	1 pc(s)	Package width	115 mm
Black toner page yield *	2200 pages	Package depth	340 mm
Colour toner page yield *	2200 pages	Package height	75 mm
Type *	Compatible	Package weight	540 g
Printing colours *	Yellow	Logistics data	
Brand compatibility *	Brother	Export Control Classification	EAR99
Supply type *	Single pack	Number (ECCN)	
Cartridge capacity	High (XL) Yield	Harmonized System (HS) code	84439990
OEM code	TN225Y/ TN245Y		



0095205066869



095205066869

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date