

Samsung CY-IGAOFSXEN Black 4K Ultra HD 3840 x 2160 pixels

Brand : Samsung

Product code: SBB-SNOWJMU/EN

Product name : CY-IGAOFSXEN

- LED S BOX
- LED HDR technology
- HDR 10+ support

Tizen 4.0, UHD (3840 X 2160), DP 1.2a, HDMI 2.0 x 2, USB
Samsung CY-IGAOFSXEN. Product colour: Black. HD type: 4K Ultra HD, Maximum video resolution: 3840 x 2160 pixels, High Dynamic Range (HDR) technology: High Dynamic Range 10+ (HDR10 Plus).
Operating system installed: Tizen 4.0. On Screen Display (OSD) languages: Arabic, Simplified Chinese, Traditional Chinese, Czech, German, English, Spanish, Finnish, French,..... Power consumption (typical): 51 W, AC input frequency: 50 / 60 Hz



Features		Ports & interfaces	
Product colour *	Black	IR input port	✓
Display		Network	
Built-in display *	✗	Ethernet LAN *	✓
Storage		Wi-Fi *	✗
Built-in storage media *	✗	Software	
Storage media type *	Not available	Operating system installed	Tizen 4.0
Video		Ergonomics	
HD type *	4K Ultra HD	On Screen Display (OSD) languages	Arabic, Simplified Chinese, Traditional Chinese, Czech, German, English, Spanish, Finnish, French, Greek, Hebrew, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Slovak, Swedish, Turkish
Maximum video resolution	3840 x 2160 pixels		
High Dynamic Range (HDR) supported *	✓		
High Dynamic Range (HDR) technology	High Dynamic Range 10+ (HDR10 Plus)		
Ports & interfaces		Power	
HDMI ports quantity *	2	Power consumption (typical)	51 W
DisplayPorts quantity	1	AC input frequency	50 / 60 Hz
Ethernet LAN (RJ-45) ports *	1	Weight & dimensions	
USB 2.0 ports quantity *	1	Weight	2.8 kg
Operational conditions			
		Operating temperature (T-T)	0 - 40 °C
		Operating relative humidity (H-H)	10 - 80%



8801643601065



8806090044939

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.