

Targus Cypress EcoSmart 39.6 cm (15.6") Briefcase Grey

Brand : Targus
Product code: TBS92502GL
Product name : Cypress EcoSmart

- Made from 14 recycled plastic water bottles
 - 1-compartment design with workstation provides ample room for your gear
 - Front stash pocket allows for quick access to small accessories
 - Padded shoulder strap for a comfortable carry
 - Luggage pass-through trolley strap
 - Soft-touch carry handles
- Cypress 15.6" Slimcase with EcoSmart, Grey

Targus Cypress EcoSmart 39.6 cm (15.6") Briefcase Grey:

Made from recyclable materials on the inside and out. Using fabric woven from 14 recycled plastic water bottles, the 15.6" Cypress Slimcase with EcoSmart® is thoughtfully designed to protect your work essentials while also protecting the environment.

Featuring a single main compartment and a convenient quick-stash pocket, it's easy to safeguard your laptop and transport your essentials in this slim, lightweight case. Plus, with three modes of transport, you can grab and go with carry handles, go hands-free with the shoulder strap, or use the trolley strap to secure on your rolling luggage.



Features		Features	
Surface coloration	Monochromatic	Country of origin	China
Maximum screen size *	39.6 cm (15.6")	Quantity	1
Case type *	Briefcase	Weight & dimensions	
Product main colour *	Grey	Width	420 mm
Integrated compartment(s)	✓	Depth	45 mm
Brand compatibility *	Any brand	Height	350 mm
Front pocket	✓	Weight	600 g
Exterior pockets	Front pocket	Notebook compartment dimensions (W x D x H)	387 x 265 x 25 mm
Carrying handle(s)	✓	Logistics data	
Shoulder strap	✓	Harmonized System (HS) code	84733080
Removable shoulder strap	✓		



5051794029864



0092636344832



092636344832

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.