



Canon GI-50 M, High Yield, Ink Bottle, Magenta

Brand : Canon **Product code:** 3404C001

Product name : GI-50 M, High Yield, Ink Bottle, Magenta



- Extend the time between top-ups and lower your running costs with a bottle of high-yield ink
 - Print up to 7,700 pages with a full set of coloured inks for greater efficiency¹
 - Cut the risk of overfilling and spillage with mess-free, no-squeeze bottles, which now come with sturdier hinged caps for reduced hassle
 - Enjoy vibrant borderless photos and bright images with Genuine Canon Ink
 - Ideal ink for topping up the Canon PIXMA G6050 and G5050
- GI-50 M, High Yield, Ink Bottle, Magenta

Canon GI-50 M, High Yield, Ink Bottle, Magenta:

Take advantage of hassle-free ink top-ups for your ink tank printer with an enhanced ink bottle. The no-squeeze design with sturdy, hinged cap ensures mess-free refills with a reduced risk of over-filling. The engineered high-yield ink also helps to lower the cost of printing per page while extending the time between refills. Expect to print up to 7,700 pages¹ with a full complement of CMY ink, ideal for those with heavy printing demands.

Features		Packaging data	
Colour ink type	Pigment-based ink	Package width	182 mm
Compatibility *	PIXMA G6050, G5050	Package depth	45 mm
Quantity per pack *	1 pc(s)	Package height	46 mm
Colour ink page yield *	7700 pages	Package weight	120 g
Type *	Original	Packaging content	
Ink type	Pigment-based ink	Sheets quantity	7700 sheets
Printing colours *	Magenta	Logistics data	
Brand compatibility *	Canon	Harmonized System (HS) code	84439990
Country of origin	Japan		



4549292134193

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.