




HP S101 Speaker Bar Stereo portable speaker Black 2.5 W



Brand : HP

Product code: 5UU40AA

Product name : S101 Speaker Bar

- Simply attach the speaker bar below your display's bottom bezel through the slots designed for a perfect fit and connect to the display's integrated USB port. No tools or software driver required.
 - Enjoy clear dual-speaker stereo sound for your media and more, and use the line-in port to connect your phone or player directly to the speaker bar. A headphone jack lets you listen without disturbing your colleagues.
 - Get the reassurance of a one-year limited warranty.^[2]
- S101 Speaker Bar

HP S101 Speaker Bar Stereo portable speaker Black 2.5 W:

More Sound. More Space.

Add rich stereo audio to select E-Series monitors, Series 5 Pro monitors and P-Series monitors^[1] and keep a clean, clutter-free desk with the HP S101 Speaker Bar, which fits neatly underneath the display head and connects through USB.

Audio		Weight & dimensions	
RMS rated power *	2.5 W	Weight *	300 g
Frequency range	140 - 200000 Hz	Packaging content	
Impedance	6 Ω	Quantity per pack	1 pc(s)
Ports & interfaces		Manual	✓
Cord length	1.8 m	Warranty card	✓
Design		Technical details	
Product type *	Stereo portable speaker	Compliance certificates	CB, EAC, Federal Communications Commission (FCC), CE, BSMI
Product design	Soundbar	General Product Safety Regulation (GPSR) URL	https://support.hp.com/us-en/document/ish_6126692-6126777-16?openCLC=true
Product colour *	Black	Logistics data	
On/off switch	✓	Harmonized System (HS) code	85182200
HP segment	Business	UNSPSC-code	43211607
Operational conditions		Total carbon footprint (kg of CO2e)	20
Operating temperature (cooling) (T-T)	5 - 35 °C	Country of origin	China
Operating relative humidity (H-H)	20 - 80%	Other features	
Weight & dimensions		Compatibility	Compatible with P22 G4, P24 G4, P22h G4, P24h G4, P27h G4, P174, P204v, E22 G4, E23 G4, E24 G4, E24q G4, E24T G4, E24i G4, E24d G4, E24u G4, E27 G4, E27d G4, E27q G4, E27u G4, HP E22 G5, E24 G5, E24t G5, E24q G5, E27 G5, E27q G5, E24u G5, E27u G5, E27k G5, E32k G5.
Width	40 mm		
Depth	274 mm		
Height	48 mm		



0193424650453



193424650453

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.