

Epson EB-1485Fi Ultra short throw projector 5000 ANSI lumens 3LCD 1080p (1920x1080) White

Brand : Epson

Product code: V11H919041

Product name : EB-1485Fi

- Flexible display options and sizes: Cater for user needs in any working environment
 - All-in-one interactive meeting display: Combines multiple resources in one interactive collaboration device
 - Increase productivity & agile working: Share and display content from a range of devices simultaneously
 - Sliding split screen: Up to four displays in one image - project images from different sources
 - Easy installation: Quick set-up with auto-adjusting calibration function
- EB-1485Fi, 3LCD, 5000 lum, 1920x1080, 16:9, 10 Bits, USB 2.0, RS-232C, RJ-45, Wi-Fi, VGA, HDMI, HDBaseT, AC 220-240 V, 458x375x210 mm



Projector		Network	
Screen size compatibility *	1651 - 3048 mm (65 - 120")	Ethernet LAN *	✓
Projection distance	0.4 - 0.4 m	Ethernet LAN (RJ-45) ports	1
Projection distance (wide)	0.6 - 0.6 m	Wi-Fi *	✓
Projector brightness *	5000 ANSI lumens	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)
Projection technology *	3LCD	Miracast	✓
Projector native resolution *	1080p (1920x1080)	Storage	
Contrast ratio (typical) *	2500000:1	Card reader integrated *	✗
Native aspect ratio *	16:9	Features	
Number of colours	1.073 billion colours	Noise level (economic mode)	28 dB
Projector brightness (economic mode)	3500 ANSI lumens	On Screen Display (OSD)	✓
Keystone correction, horizontal	-3 - 3°	Screen mirroring	✓
Keystone correction, vertical	-3 - 3°	Noise level *	37 dB
Heat dissipation	1244 BTU/h	Air filter	✓
Light source		Composite sync	✓
Light source type *	Laser	Country of origin	China
Service life of light source *	20000 h	Password protection	✓
Service life of light source (economic mode)	30000 h	Compatible operating systems	Linux, Mac OS 10.10.x, Mac OS 10.7.x, Mac OS 10.8.x, Mac OS 10.9.x, Ubuntu 14.10, Ubuntu 15.04
Lens system		Multimedia	
Focus *	Manual	Built-in speaker(s) *	✓
Fixed focal length	39 mm	RMS rated power	16 W
Aperture range (F-F)	1.5 - 1.5	Design	
Zoom capability	✓	Market positioning *	Presentation
Zoom type	Auto	Product type *	Ultra short throw projector
Zoom ratio	1.35:1	Product colour *	White
Video		Placement	Wall
Full HD *	✓	Cable lock slot	✓
3D *	✗	Cable lock slot type	Kensington
Supported graphics resolutions	1920 x 1080 (HD 1080)	Display	
Supported video modes	1080p	Built-in display *	✗
Video colour modes	Blackboard, Cinema, Dynamic, Presentation, sRGB		
Adjustable colour temperature	✓		

Ports & interfaces		Power	
HDMI connector type	Full-size	Power source *	AC
HDBaseT port	✓	Power consumption (typical) *	366 W
USB 2.0 ports quantity	2	Power consumption (standby) *	0.5 W
USB 2.0 Type-B ports quantity	2	Power consumption (economy mode)	262 W
Microphone in	✓	AC input voltage	220 - 240 V
Serial interface type *	RS-232C	AC input frequency	50 - 60 Hz
PC Audio in	✓	Operational conditions	
PC Audio out	✓	Storage temperature (T-T)	-10 - 60 °C
VGA (D-Sub) ports quantity *	2	Weight & dimensions	
HDMI ports quantity *	3	Width	458 mm
Component video (YPbPr/YCbCr) in *	1	Depth	210 mm
DVI port *	✗	Height	375 mm
DC-in jack	✓	Weight *	9.3 kg
Network		Package width	472 mm
Smart TV *	✗	Package depth	590 mm
		Package height	640 mm
		Package weight	27.7 kg
		Packaging content	
		Remote control included *	✓
		Manual	✓
		Logistics data	
		Quantity per pack	1 pc(s)



8715946673752

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.