

StarTech.com 2 Port USB 3.0 A Female Slot Plate Adapter

Brand : StarTech.com

Product code: USB3SPLATE

Product name : 2 Port USB 3.0 A Female Slot Plate Adapter

StarTech.com 2 Port USB 3.0 A Female Slot Plate Adapter

StarTech.com 2 Port USB 3.0 A Female Slot Plate Adapter:

The USB3SPLATE 2-Port USB 3.0 A Slot Plate converts the USB pins on the USB 3.0 motherboard header to 2 standard USB 3.0 A-type ports. The plate can be mounted on the rear panel of a computer case, adding two USB 3.0 A female ports for simple connection to USB peripheral devices.

The USB 3.0 standard supports transfer rates of up to 5Gbps, and provides connectivity and support for older USB 2.0 (480Mbps) and 1.1 (12Mbps) devices.

The StarTech.com Advantage

Adds two USB 3.0 ports for faster transfer rates with USB 3.0 devices, while still supporting USB 2.0 and USB 1.1 devices

Easy to use and install

Backed by StarTech.com lifetime warranty



Ports & interfaces		Weight & dimensions	
Host interface *	IDC	Depth	500 mm
Output interface *	USB 3.2 Gen 1 (3.1 Gen 1)	Weight	72 g
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	2	Packaging data	
Design		Package width	125 mm
Internal *	✓	Package depth	225 mm
Product colour	Blue, Stainless steel	Package height	18 mm
Maximum cable length	0.5 m	Package weight	77 g
Certification	CE, REACH	Logistics data	
Technical details		Harmonized System (HS) code	84733020
		Other features	
Compliance certificates	RoHS	Material	PVC



0065030845281



065030845281



5054629278468

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.