

Targus TBR038GL luggage Trolley Charcoal 24 L

Brand : Targus
Product code: TBR038GL
Product name : TBR038GL

- Lightweight, easy-to-grasp single pole handle
 - Smooth, quiet wheels for easy maneuvering
 - SafePort® Sling suspends laptops for added drop protection
- 12-15.6" CitySmart Compact Under-Seat Roller

Targus TBR038GL luggage Trolley Charcoal 24 L:

Get smart travel organization with the 12-15.6" CitySmart™ Compact Under-Seat Roller. For on-the-go professionals who value convenience and style, this hardworking roller provides the ideal space, convenience, and features for short haul trips. Safeguard your style with a separate clothing compartment. Protect your laptop in the drop-protective SafePort® Sling. Retractable top and side handles help you hoist overhead or grab from under your seat with ease. Smooth-rolling and quiet wheels combined with a sturdy trolley pole let you maneuver masterfully. Park it with ease thanks to the large stand-up base. Eye-catching orange interior elements highlight the laptop SafePort® Sling, accessories pouches and more, for easy visibility and added style.



Features		Weight & dimensions	
Luggage type *	Trolley	Luggage bag depth	20.3 cm
Product main colour *	Charcoal	Luggage bag height	40.6 cm
Bag size	Compact	Luggage bag weight	2.8 kg
Number of wheels	2 wheel(s)	Height	430 mm
Number of luggage bags	1 pc(s)	Width	330 mm
Retractable handle	✓	Depth	205 mm
Notebook compartment	✓	Weight	2.81 kg
Maximum screen size	40.6 cm (16")	Logistics data	
Bottle holder	✓	Harmonized System (HS) code	42029291
Tablet compartment	✓	Master (outer) case width	360 mm
Exterior pockets	Front pocket	Master (outer) case length	470 mm
Interior pocket	✓	Master (outer) case height	475 mm
Closure type	Zipper	Master (outer) case gross weight	6.32 kg
Weight & dimensions		Products per master (outer) case	2 pc(s)
Volume *	24 L		
Luggage bag width	30.5 cm		



0092636333928



092636333928



5051794026153

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.