

## ASUS VP248QG computer monitor 61 cm (24") 1920 x 1080 pixels Full HD Black

**Brand :** ASUS

**Product code:** 90LM0480-B02170

**Product name :** VP248QG

- 24-inch Full HD monitor with 1ms (GTG) quick response time and 75Hz refresh rate for fast and smooth gaming
  - Features Adaptive-Sync/FreeSync™ technology to eliminate screen tearing and choppy frame rates
  - ASUS-exclusive GamePlus with crosshair, timer, FPS counter, display alignment functions for in-game enhancements
  - Extensive connectivity including DisplayPort, HDMI and D-sub ports. Plus 1.5-Watt stereo speakers
  - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- 24" Full HD 1920 x 1080, 1 ms, 16.7M, 3W RMS, 27 W, 100 - 240 V, 50/60 Hz  
 ASUS VP248QG. Display diagonal: 61 cm (24"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display surface: Matt, Response time: 1 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 170°, Viewing angle, vertical: 170°. Built-in speaker(s). VESA mounting. Product colour: Black



| Display                      |                       | Ergonomics                                |              |
|------------------------------|-----------------------|-------------------------------------------|--------------|
| Display diagonal *           | 61 cm (24")           | VESA mounting *                           | ✓            |
| Display resolution *         | 1920 x 1080 pixels    | Panel mounting interface                  | 100 x 100 mm |
| HD type *                    | Full HD               | Cable lock slot *                         | ✓            |
| Native aspect ratio *        | 16:9                  | Cable lock slot type                      | Kensington   |
| Panel type *                 | TN                    | Height adjustment *                       | ✗            |
| Touchscreen *                | ✗                     | Tilt adjustment                           | ✓            |
| Display brightness (typical) | 250 cd/m²             | Tilt angle range                          | -5 - 20°     |
| Response time *              | 1 ms                  |                                           |              |
| Display surface              | Matt                  |                                           |              |
| Screen shape *               | Flat                  |                                           |              |
| Contrast ratio (typical) *   | 1000:1                |                                           |              |
| Maximum refresh rate *       | 60 Hz                 |                                           |              |
| Viewing angle, horizontal    | 170°                  |                                           |              |
| Viewing angle, vertical      | 170°                  |                                           |              |
| Display number of colours *  | 16.78 million colours |                                           |              |
| Pixel pitch                  | 0.2768 x 0.2768 mm    |                                           |              |
| Digital horizontal frequency | 24 - 84 kHz           |                                           |              |
| Digital vertical frequency   | 48 - 75 Hz            |                                           |              |
| 3D                           | ✗                     |                                           |              |
| Performance                  |                       | Power                                     |              |
| AMD FreeSync *               | ✓                     | Energy efficiency class (SDR) *           | F            |
| AMD FreeSync type            | FreeSync              | Energy consumption (SDR) per 1000 hours * | 21 kWh       |
| VESA Adaptive Sync support   | ✓                     | Power consumption (typical) *             | 21.1 W       |
| Flicker-free technology      | ✓                     | Power consumption (standby) *             | 0.3 W        |
| Multimedia                   |                       | Power consumption (off)                   | 0.2 W        |
| Number of speakers           | 2                     | AC input voltage                          | 100 - 240 V  |
| RMS rated power              | 3 W                   | AC input frequency                        | 50 - 60 Hz   |
| Built-in speaker(s) *        | ✓                     | Energy efficiency scale                   | A to G       |
| Built-in camera *            | ✗                     |                                           |              |
| Design                       |                       | Weight & dimensions                       |              |
| Market positioning *         | Gaming                | Width (with stand)                        | 571.1 mm     |
| Product colour *             | Black                 | Depth (with stand)                        | 199.4 mm     |
|                              |                       | Height (with stand)                       | 405.8 mm     |
|                              |                       | Weight (with stand)                       | 3.6 kg       |
|                              |                       | Width (without stand)                     | 571.1 mm     |
|                              |                       | Depth (without stand)                     | 51.7 mm      |
|                              |                       | Height (without stand)                    | 341.5 mm     |
|                              |                       | Weight (without stand)                    | 2.95 kg      |
|                              |                       | Packaging data                            |              |
|                              |                       | Package width                             | 625 mm       |
|                              |                       | Package depth                             | 135 mm       |
|                              |                       | Package height                            | 461 mm       |
|                              |                       | Package weight                            | 5.7 kg       |

| Ports & interfaces         |   | Other features              |                                                                                                                                                                                                           |  |
|----------------------------|---|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Built-in USB hub *         | ✗ | TV tuner integrated         | ✗                                                                                                                                                                                                         |  |
| VGA (D-Sub) ports quantity | 1 | Certification               | UL/cUL, Energy Star®, VCCI, MEPS, CCC, BSMI, CEL level 1, RCM, CB, WHQL (Windows 7, Windows 10, Windows 8.1), TUV Flicker-free , PSE, J-MOSS, PSB, KC , ErP, TUV Low Blue Light, FCC, WEEE, KCC, eStandby |  |
| DVI port                   | ✗ |                             |                                                                                                                                                                                                           |  |
| HDMI ports quantity        | 1 |                             |                                                                                                                                                                                                           |  |
| DisplayPorts quantity      | 1 |                             |                                                                                                                                                                                                           |  |
| Headphone out *            | ✓ | <b>Logistics data</b>       |                                                                                                                                                                                                           |  |
| Headphone outputs          | 1 |                             |                                                                                                                                                                                                           |  |
|                            |   | Harmonized System (HS) code | 85285210                                                                                                                                                                                                  |  |



4718017043748



0192876043707



192876043707

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.