

Epson Bond Paper White 80, 841mm x 50m

Brand : Epson

Product code: C13S045274

Product name : Bond Paper White 80, 841mm x 50m



Bond Paper White 80, 841mm x 50m

Epson Bond Paper White 80, 841mm x 50m:

This paper is ideal for everyday plotting, technical drawings and illustrations. It shows crisp lines, high-contrast colour and sharp-looking characters from 1mm in size upwards, and is suitable for both dye and pigment inks.

- CAD paper ideal for everyday plotting
- Shows sharp lines and high-contrast colour
- Works well with dye and pigment ink
- Suitable for 100-year archival
- Meets ISO 9706 standard

Epson Bond Paper White 80, 841mm x 50m. Media weight: 80 g/m², Product colour: White, Certification: ISO 9706. Roll width: 81.4 cm, Roll length: 50 m. Quantity per pack: 1 pc(s), Package width: 107 mm, Package depth: 935 mm. Pallet width (UK): 100 cm, Pallet length (UK): 120 cm, Pallet height (UK): 3.55 m. Country of origin: Germany

Features		Packaging data	
Product colour	White	Package weight	3.55 kg
Media weight *	80 g/m²	Logistics data	
Certification	ISO 9706	Harmonized System (HS) code	37032000
Compatible products	- SureColor SC-T7200D-PS -	Pallet width (UK)	100 cm
	SureColor SC-T7200D - SureColor	Pallet length (UK)	120 cm
	SC-T7200-PS - SureColor SC-T7200 -	Pallet height (UK)	3.55 m
	SureColor SC-P20000 - Epson	Pallet gross width	80 cm
	SureColor SC-T7000 - Epson Stylus	Pallet gross length	120 cm
	Pro 9890 SpectroProofer - Epson	Pallet gross height	3.55 m
	Stylus Pro 9890 - Epson Stylus Pro	Products per pallet	60 pc(s)
Weight & dimensions		Products per pallet (UK)	80 pc(s)
Roll width	81.4 cm	Products per pallet layer	6 pc(s)
Roll length	50 m	Products per pallet layer (UK)	8 pc(s)
Packaging data		Minimum order quantity	4 pc(s)
Quantity per pack	1 pc(s)	Other features	
Package width	107 mm	Country of origin	Germany
Package depth	935 mm		
Package height	107 mm		



8715946490717

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.