

ASUS ZenScreen MB16AHP computer monitor 39.6 cm (15.6") 1920 x 1080 pixels Full HD LED Black



Brand : ASUS

Product family: ZenScreen

Product code: 90LM04T0-B01170

Product name : MB16AHP

- USB-C and micro-HDMI ports provide versatile connectivity with smartphones, laptops, game consoles, and cameras
 - Built in powerful battery, support display to sustain the power for up to 4 hours, enables in connection with not only laptops but further mobile phones
 - Can automatically sense its orientation and switch the monitor between landscape and portrait modes
 - Just 860g and only 9mm thin, it helps you get things done more efficiently when you're on the go
 - Foldable smart case can be turned into a stand to prop the monitor up in either portrait or landscape mode
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- Portable USB Type-C 15.6" Monitor, IPS, 1920x1080px, 250 cd/m², 800:1, 2x 1W, Micro HDMI, Li-Po 7800 mAh

Display		Ergonomics	
Display diagonal *	39.6 cm (15.6")	VESA mounting *	×
Display resolution *	1920 x 1080 pixels	Cable lock slot *	×
HD type *	Full HD	Height adjustment *	×
Native aspect ratio *	16:9	Power	
Display technology *	LED	Energy efficiency class (SDR) *	F
Panel type *	IPS	Energy consumption (SDR) per 1000 hours *	13 kWh
Touchscreen *	×	Power consumption (typical) *	13 W
Display brightness (peak)	250 cd/m²	Power consumption (standby) *	0.5 W
Display brightness (typical)	220 cd/m²	Power consumption (off)	0.3 W
Response time *	5 ms	Energy efficiency scale	A to G
Screen shape *	Flat	Operational conditions	
Contrast ratio (dynamic)	800:1	Operating temperature (T-T)	5 - 35 °C
Maximum refresh rate *	60 Hz	Operating relative humidity (H-H)	20 - 90%
Pixel pitch	0.179 x 0.179 mm	Weight & dimensions	
Viewable size, horizontal	34.4 cm	Width (with stand)	359.7 mm
Viewable size, vertical	19.4 cm	Depth (with stand)	9 mm
3D	×	Height (with stand)	227.4 mm
Performance		Weight (with stand)	860 g
NVIDIA G-SYNC *	×	Packaging data	
AMD FreeSync *	×	Package width	485 mm
Flicker-free technology	✓	Package height	305 mm
Multimedia		Package weight	3.1 kg
Number of speakers	2	Package type	Box
RMS rated power	2 W	Packaging content	
Built-in speaker(s) *	✓	Cables included	Micro-HDMI to HDMI, USB Type-C
Built-in camera *	×	Quick start guide	✓
Design		Other features	
Market positioning *	Business	AC adapter included	✓
Product colour *	Black	On/off switch	✓
Ports & interfaces		TV tuner integrated	×
Built-in USB hub *	×	Logistics data	
DVI port	×	Harmonized System (HS) code	85285210
HDMI *	×		
Micro HDMI ports quantity	1		

Ports & interfaces

Audio input	×
Headphone out *	×



4718017258470



0192876315507



192876315507



4718017315531



0192876258477



192876258477



4718017315500

Catalog Object Cloud



Disclaimer: The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.