



Canon i-SENSYS MF543x Laser A4 1200 x 1200 DPI 43 ppm Wi-Fi

Brand : Canon

Product family: i-SENSYS

Product code: 3513C013

Product name : MF543x

Print/Copy/Scan/Fax, USB 2.0, 802.11b/g/n, LAN, 800MHz x 2, 1GB, 12.7 cm LCD Touchscreen

[Canon i-SENSYS MF543x Laser A4 1200 x 1200 DPI 43 ppm Wi-Fi:](#)

Canon i-SENSYS MF540 Series

Get ultra-fast results and versatile multifunctionality from a space-saving black and white laser printer, ideal for hard-working businesses

A versatile black and white laser printer

Meet the needs of your business with the Canon i-SENSYS MF540 series: high-performance multifunctional laser printers with rapid print speeds, customisable controls and flexible mobile connectivity – perfect for those in need of a space-saving solution.

Canon i-SENSYS MF543x. Print technology: Laser, Printing: Mono printing, Maximum resolution: 1200 x 1200 DPI. Copying: Mono copying, Maximum copy resolution: 600 x 600 DPI. Scanning: Colour scanning, Optical scanning resolution: 600 x 600 DPI. Faxing: Mono faxing. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: Black, White



Printing		Paper handling	
Duplex printing mode	Auto	Non-ISO print media sizes	16K, Executive, Index card, Legal, Letter, Oficio, Statement
Print technology *	Laser	Envelopes sizes	C5, Com-10, DL, Monarch
Printing *	Mono printing	Custom media width	76.2 - 216 mm
Duplex printing *	✓	Custom media length	127 - 355.6 mm
Maximum resolution *	1200 x 1200 DPI	Paper tray media weight	60 - 120 g/m ²
Print speed (black, normal quality, A4/US Letter) *	43 ppm	Multi-Purpose Tray media weight	60 - 199 g/m ²
Warm-up time	14 s	Ports & interfaces	
Time to first page (black, normal)	5.7 s	Direct printing *	✓
Secure printing	✓	USB port	✓
Copying		USB 2.0 ports quantity	1
Duplex copying *	✓	Network	
Copying *	Mono copying	Wi-Fi *	✓
Maximum copy resolution *	600 x 600 DPI	Ethernet LAN *	✓
Copy speed (black, normal quality, A4)	43 cpm	Cabling technology	10/100/1000Base-T(X)
Maximum number of copies	999 copies	Ethernet LAN data rates	10,100,1000 Mbit/s
Copier resize	25 - 400%	Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
N-in-1 copy function	✓	Near Field Communication (NFC)	✓
N-in-1 copy function (N=)	2, 4	Security algorithms	64-bit WEP, 128-bit WEP, 802.1x RADIUS, HTTPS, IPPS, SNMPv3, SSL/TLS, TKIP, WPA-PSK, WPA2-PSK
ID-card copy function	✓	Supported network protocols (IPv4)	LPD, RAW, Port9100, IPP, IPPS, WSD
Scanning		Supported network protocols (IPv6)	LPD, RAW, Port9100, IPP, IPPS, WSD
Duplex scanning *	✓	Management protocols	SNMPv1, SNMPv3 (IPv4,IPv6)
Scanning *	Colour scanning	Mobile printing technologies	Apple AirPrint, Canon PRINT Business, Google Cloud Print, Mopria Print Service
Optical scanning resolution *	600 x 600 DPI	Performance	
Maximum scan resolution	9600 x 9600 DPI	Internal memory *	1000 MB
Scanner type *	Flatbed & ADF scanner	Processor frequency	800 MHz
Scan to	Cloud, E-mail	Processor cores	2
Image formats supported	JPEG, PNG, TIFF	Sound pressure level (printing)	72.9 dB
Document formats supported	PDF	Design	
Input colour depth	24 bit	Product colour *	Black, White
Output colour depth	24 bit	Market positioning *	Home & office
Greyscale levels	256		
Scan drivers	ICA, TWAIN, WIA		

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date



8714574663845

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.