

Philips V Line 222V8LA/00 computer monitor 54.6 cm (21.5") 1920 x 1080 pixels Full HD LCD Black

Brand : Philips

Product family: V Line

Product code: 222V8LA/00

Product name : 222V8LA/00

222V8LA LCD monitor

Philips V Line 222V8LA/00 computer monitor 54.6 cm (21.5") 1920 x 1080 pixels Full HD LCD Black:

Philips V line wide-view monitor gives viewing beyond boundaries, great value with essential features. Adaptive-Sync provides flawless viewing without screen tearing. Features like LowBlue mode and flicker-free for easy-on-the eyes.

Philips V Line 222V8LA/00. Display diagonal: 54.6 cm (21.5"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LCD, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). VESA mounting. Product colour: Black



Display		Ergonomics	
Display diagonal *	54.6 cm (21.5")	Cable lock slot type	Kensington
Display resolution *	1920 x 1080 pixels	Height adjustment *	✗
HD type *	Full HD	Tilt adjustment	✓
Native aspect ratio *	16:9	Tilt angle range	-5 - 20°
Display technology *	LCD	On Screen Display (OSD)	✓
Panel type *	VA	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Backlight type	W-LED		
Touchscreen *	✗		
Display brightness (typical)	250 cd/m²	Number of OSD languages	21
Response time *	4 ms	Plug and Play	✓
Screen shape *	Flat	LED indicators	Operation, Stand-by
Aspect ratio	16:9	Power	
Contrast ratio (typical) *	3000:1	Energy efficiency class (SDR) *	D
Dynamic contrast ratio marketing name	Mega Infinity DCR	Energy consumption (SDR) per 1000 hours *	12 kWh
Maximum refresh rate *	75 Hz	Power consumption (typical) *	13.3 W
Viewing angle, horizontal	178°	Power consumption (standby) *	0.5 W
Viewing angle, vertical	178°	Power consumption (off)	0.3 W
Display number of colours *	16.7 million colours	AC input voltage	100 - 240 V
Pixel pitch	0.2493 x 0.241 mm	AC input frequency	50 - 60 Hz
Pixel density	102 ppi	Power supply type	Internal
Horizontal scan range	30 - 85 kHz	Energy efficiency scale	A to G
Vertical scan range	48 - 75 Hz	Operational conditions	
Viewable size, horizontal	47.9 cm	Operating temperature (T-T)	0 - 40 °C
Viewable size, vertical	26 cm	Storage temperature (T-T)	-20 - 60 °C
Digital horizontal frequency	30 - 85 kHz	Operating relative humidity (H-H)	20 - 80%
Digital vertical frequency	48 - 75 Hz	Operating altitude	0 - 3658 m
Sync-on-green (SOG)	✓	Non-operating altitude	0 - 12192 m
Display diagonal (metric)	54.6 cm		
DDC/CI	✓		
Haze rate	25%		

Display		Weight & dimensions	
Surface hardness	3H	Width (with stand)	493 mm
Display sRGB	✓	Depth (with stand)	220 mm
Performance		Height (with stand)	369 mm
NVIDIA G-SYNC *	✗	Weight (with stand)	2.79 kg
AMD FreeSync *	✗	Width (without stand)	493 mm
VESA Adaptive Sync support	✓	Depth (without stand)	44 mm
Component video sync	Separate Sync, Sync-on-green (SOG)	Height (without stand)	286 mm
Flicker-free technology	✓	Weight (without stand)	2.4 kg
Low Blue Light technology	✓	Packaging data	
Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1	Package width	565 mm
Mac operating systems supported	Mac OS X 10.0 Cheetah, Mac OS X 10.1 Puma, Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina, Mac OS X 10.2 Jaguar, Mac OS X 10.3 Panther, Mac OS X 10.4 Tiger, Mac OS X 10.5 Leopard, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks, Mac OS X 11.0 Big Sur	Package depth	111 mm
		Package height	440 mm
Multimedia		Package weight	3.87 kg
Number of speakers	2	Packaging content	
RMS rated power	2 W	Stand included	✓
Built-in speaker(s) *	✓	Cables included	HDMI, AC
Built-in camera *	✗	Manual	✓
Design		Sustainability	
Product colour *	Black	Sustainability certificates	ENERGY STAR, TCO
Ports & interfaces		Other features	
Built-in USB hub *	✗	Exterior finish type	Textured
DVI port	✗	Picture enhancement	SmartImage
HDMI *	✓	Regulatory Approvals	UKRAINIAN; CB; TUV/GS; TUV Ergo; CU-EAC; EAEU RoHS; CE Mark
HDMI ports quantity	1.4	Heavy metals free	Hg (mercury)
HDMI version	1.4	EasyRead mode	✓
DisplayPorts quantity	1.2	LowBlue mode	✓
DisplayPort version	1.2	Energy efficiency class (old)	E
Audio input	✗	Compliance certificates	RoHS
Headphone out *	✓	Mean time between failures (MTBF)	50000 h
PC Audio in	✓	Certification	UKRAINIAN, CB, TUV/GS, TUV Ergo, CU-EAC, EAEU RoHS, CE Mark
DC-in jack	✓	Recycling data	
Ergonomics		Recyclable packaging material	100%
VESA mounting *	✓	Logistics data	
Panel mounting interface	100 x 100 mm	Harmonized System (HS) code	85285210
Cable lock slot *	✓		



8712581771690

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.