



BenQ InstaShow WDC10 wireless presentation system HDMI Desktop

Brand : BenQ

Product code: 9H.JF878.N5E

Product name : InstaShow WDC10

- Easy-to-use wireless presentation device / InstaShow® WDC10
- One simple button to start presenting
- No software installation or maintenance
- 802.11ac wireless connection

AES 128, 1920x1080, HDMI 1.4, Black

BenQ InstaShow WDC10. Form factor: Desktop, Product colour: Black. Maximum resolution (HDMI): 1920 x 1080 pixels, Supported video modes: 1080p. Antenna type: External. Wi-Fi standards: Wi-Fi 5 (802.11ac), Wi-Fi data rate (max): 867 Mbit/s, Top Wi-Fi standard: Wi-Fi 5 (802.11ac). Interface: HDMI



Design		Power	
Form factor *	Desktop	Power source type *	USB
Product colour	Black	Input voltage	5 V
LED indicators	✓	Input current	1.5 A
Features		Power consumption (typical)	5 W
Maximum resolution (HDMI)	1920 x 1080 pixels	System requirements	
Supported video modes	1080p	Windows operating systems supported	✓
Number of simultaneously connected devices (max)	16	Weight & dimensions	
Antenna		Weight	1.27 kg
Antenna type	External	Package width	390 mm
Antennas quantity	2	Package depth	485 mm
Network		Package height	205 mm
Wi-Fi standards	Wi-Fi 5 (802.11ac)	Package weight	7.6 kg
Wi-Fi data rate (max)	867 Mbit/s	Packaging content	
Top Wi-Fi standard	Wi-Fi 5 (802.11ac)	AC adapter included	✓
Frequency band	5 GHz	Cables included	HDMI, USB Type-A
Security algorithms	128-bit AES, WPA2	Quick start guide	✓
Ports & interfaces		Logistics data	
Interface *	HDMI	Country of origin	Taiwan
Number of HDMI outputs	1	Products per pallet	144 pc(s)
HDMI version	1.4	Harmonized System (HS) code	8517620000



4718755072420

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.