

ASUS MB14AC computer monitor 35.6 cm (14") 1920 x 1080 pixels Full HD Grey

Brand : ASUS

Product code: 90LM0631-B01170

Product name : MB14AC

- Features a hybrid-signal solution that supports power and video transmission, and enables compatibility with any laptop with a USB Type-C or Type A port
 - Can automatically sense its orientation and switch the monitor between landscape and portrait modes
 - 14-inch Full HD portable anti-glare IPS display with an ultra-slim design helps you get things done more efficiently when you're on the go
 - Foldable smart case can be turned into a stand to prop the monitor up in either portrait or landscape mode
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- 14", 1920x1080, 60Hz, IPS, 5ms, Flicker-free, HDCP 1.4, USB C, 324.94x208.03x11.2mm
 ASUS MB14AC. Display diagonal: 35.6 cm (14"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Product colour: Grey



Display		Network	
Display diagonal *	35.6 cm (14")	Wi-Fi	×
Display resolution *	1920 x 1080 pixels	Ergonomics	
HD type *	Full HD	VESA mounting *	×
Native aspect ratio *	16:9	Cable lock slot *	×
Panel type *	IPS	Height adjustment *	×
Touchscreen *	×	LED indicators	✓
Display brightness (typical)	250 cd/m²	Power	
Response time *	5 ms	Energy efficiency class (SDR) *	B
Screen shape *	Flat	Energy consumption (SDR) per 1000 hours *	5 kWh
Supported graphics resolutions	640 x 480 (VGA), 800 x 600 (SVGA), 1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 960, 1440 x 900 (WXGA+), 1680 x 1050 (WSXGA+), 1920 x 1080 (HD 1080)	Power consumption (typical) *	7 W
		Power consumption (off)	0 W
Aspect ratio	16:9	Power consumption (PowerSave)	0 W
Contrast ratio (typical) *	700:1	Energy efficiency scale	A to G
Maximum refresh rate *	60 Hz	Operational conditions	
Viewing angle, horizontal	178°	Operating temperature (T-T)	0 - 40 °C
Viewing angle, vertical	178°	Weight & dimensions	
Display number of colours *	16.78 million colours	Width (with stand)	324.9 mm
Pixel pitch	0.16 x 0.16 mm	Depth (with stand)	11.2 mm
Viewable size, horizontal	30.9 cm	Height (with stand)	208 mm
Viewable size, vertical	17.4 cm	Weight (with stand)	590 g
Viewable size diagonal	35.6 cm	Packaging data	
Performance		Package width	392 mm
Flicker-free technology	✓	Package depth	77 mm
Low Blue Light technology	✓	Package height	257 mm
Multimedia		Package weight	1.3 kg
Built-in speaker(s) *	×	Packaging content	
Built-in camera *	×	Cables included	USB Type-C to USB Type-C
Design			
Market positioning *	Business		

Design		Other features	
Product colour *	Grey	Certification	BSMI, CB, CCC, CU, FCC, J-MOSS, KCC, UkrSEPRO, UL/cUL, VCCI, WEEE, WHQL (Windows 10, Windows 8.1, Windows 7), TUV Flicker-free, TUV Low Blue Light, RCM
Ports & interfaces			
USB Type-C DisplayPort Alternate Mode	✓		
DVI port	✗		
HDMI *	✗	Logistics data	Harmonized System (HS) code 85285210
Audio input	✗		
Headphone out *	✗		
HDCP	✓		



4718017690607



0192876690567



192876690567



5715328234000

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.