

Epson EcoTank ET-M1180 inkjet printer 1200 x 2400 DPI A4 Wi-Fi

Brand : Epson

Product family: EcoTank

Product code: C11CG94402BY

Product name : ET-M1180

- Low TCO and energy use: Keep your printing costs extremely low
- High ink yields: Print up to 11,000 pages with the included ink
- Save time: Fast FPOT
- Built for business: Duplex printing and PCL support
- Easy connectivity: Wi-Fi, USB and Ethernet

A4, Monochrome, Inkjet, 1200 x 2400DPI, PCL5e, USB, Wi-Fi, Ethernet

Epson EcoTank ET-M1180. Maximum duty cycle: 20000 pages per month. Maximum resolution: 1200 x 2400 DPI. Maximum ISO A-series paper size: A4. Print speed (black, normal quality, A4/US Letter): 39 ppm. Duplex printing. Wi-Fi. Product colour: Black, White



Features		Paper handling	
Recommended duty cycle	250 - 1500 pages per month	Paper tray media weight	64 - 256 g/m ²
Duplex printing *	✓	Ports & interfaces	
Page description languages *	PCL 5e	USB port *	✓
Colour *	✗	Standard interfaces	Ethernet, USB, Wireless LAN
Maximum duty cycle *	20000 pages per month	Network	
Printing		Ethernet LAN *	✓
Maximum resolution *	1200 x 2400 DPI	Wi-Fi *	✓
Print speed (black, normal quality, A4/US Letter) *	39 ppm	Wi-Fi Direct *	✓
Time to first page (black, normal)	6 s	Design	
Duplex print speed (black, normal quality, A4/US Letter)	9 ppm	Market positioning *	Home & office
Input & output capacity		Product colour *	Black, White
Total number of input trays *	2	Power	
Total input capacity *	251 sheets	Power consumption (printing) *	14 W
Total output capacity *	100 sheets	System requirements	
Maximum input capacity	251 sheets	Windows operating systems supported	✓
Paper handling		Mac operating systems supported	✓
Maximum ISO A-series paper size *	A4	Server operating systems supported	Windows Server 2008, Windows Server 2008 R2, Windows Server 2008 x64, Windows Server 2012 R2, Windows Server 2012 x64, Windows Server 2016
Paper tray media types *	Plain paper	Weight & dimensions	
Multi-purpose tray media types	Plain paper	Width	375 mm
ISO A-series sizes (A0...A9) *	A4, A5, A6	Depth	347 mm
Non-ISO print media sizes	Legal	Height	151 mm
		Weight	4.3 kg
		Logistics data	
		Harmonized System (HS) code	84433210



8715946655291

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.