

Philips E Line 325E1C/00 computer monitor 80 cm (31.5") 2560 x 1440 pixels Quad HD LCD Black

Brand : Philips

Product family: E Line

Product code: 325E1C/00

Product name : 325E1C/00

- Curved display design for a more immersive experience
 - Ultra Wide-Color wider range of colours for a vivid picture
 - VA display delivers awesome images with wide viewing angles
 - Crystal clear images with Quad HD 2560 x 1440 pixels
 - SmartContrast for rich black details
 - SmartImage game mode optimised for gamers
 - Less eye fatigue with Flicker-Free technology
 - LowBlue Mode for easy-on-the-eyes productivity
 - HDMI ensures universal digital connectivity
 - DisplayPort connection for maximum visuals
 - Mercury Free eco-friendly display
- 325E1C Curved LCD monitor with Ultra Wide-Color



Philips E Line 325E1C/00 computer monitor 80 cm (31.5") 2560 x 1440 pixels Quad HD LCD Black:

The 32" curved E line display offers a truly immersive experience in a stylish design. Crystal-clear QHD with Ultra Wide-Color and AMD FreeSync technology brings your images to life!

Display		Ergonomics	
Display diagonal *	80 cm (31.5")	Panel mounting interface	100 x 100 mm
Display resolution *	2560 x 1440 pixels	Cable lock slot *	✓
HD type *	Quad HD	Cable lock slot type	Kensington
Native aspect ratio *	16:9	Height adjustment *	✗
Display technology *	LCD	Tilt adjustment	✓
Panel type *	VA	Tilt angle range	-5 - 20°
LED backlight	✓	On Screen Display (OSD)	✓
Backlight type	W-LED	On Screen Display (OSD) languages	Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
Touchscreen *	✗		
Display brightness (typical)	250 cd/m²		
Response time *	4 ms		
Anti-glare screen	✓	Number of OSD languages	21
Screen shape *	Curved	Plug and Play	✓
Screen curvature rating	1500R	LED indicators	Operation, Stand-by
Supported graphics resolutions	2560 x 1440	Power	
Aspect ratio	16:9	Energy efficiency class (SDR) *	F
Contrast ratio (typical) *	3000:1	Energy consumption (SDR) per 1000 hours *	32 kWh
Dynamic contrast ratio marketing name	Mega Infinity	Power consumption (typical) *	47.3 W
Maximum refresh rate *	75 Hz	Power consumption (standby) *	0.5 W
Viewing angle, horizontal	178°	Power consumption (off)	0.3 W
Viewing angle, vertical	178°	AC input voltage	100 - 240 V
Display number of colours *	16.7 million colours	AC input frequency	50/60 Hz
Pixel pitch	0.272 x 0.272 mm	Power supply type	Internal
Pixel density	93 ppi	Energy efficiency scale	A to G
Horizontal scan range	70 - 115 kHz		
Vertical scan range	48 - 75 Hz		
Viewable size, horizontal	69.7 cm		
Viewable size, vertical	39.2 cm		

Display		Operational conditions	
Digital horizontal frequency	70 - 115 kHz	Operating temperature (T-T)	0 - 40 °C
Digital vertical frequency	48 - 75 Hz	Storage temperature (T-T)	-20 - 60 °C
Sync-on-green (SOG)	✓	Operating relative humidity (H-H)	20 - 80%
Display diagonal (metric)	80 cm	Operating altitude	0 - 3658 m
DDC/CI	✓	Non-operating altitude	0 - 12192 m
Haze rate	25%	Weight & dimensions	
Surface hardness	3H	Width (with stand)	709 mm
Colour gamut standard	sRGB	Depth (with stand)	281 mm
Colour gamut	102%	Height (with stand)	523 mm
sRGB coverage (typical)	123%	Weight (with stand)	7.34 kg
NTSC coverage (typical)	102%	Width (without stand)	709 mm
Screen curvature	150 cm	Depth (without stand)	88 mm
3D	✗	Height (without stand)	425 mm
Separate H/V sync	✓	Weight (without stand)	6.52 kg
Display sRGB	✓	Packaging data	
Display panel size	31.5 inch/80 cm	Package width	800 mm
Performance		Package depth	236 mm
NVIDIA G-SYNC *	✗	Package height	625 mm
AMD FreeSync *	✓	Package weight	10.2 kg
Component video sync	Separate Sync, Sync-on-green (SOG)	Packaging content	
Flicker-free technology	✓	Stand included	✓
Low Blue Light technology	✓	Cables included	HDMI, AC
		Manual	✓
Multimedia		Other features	
Built-in speaker(s) *	✗	Compatible operating systems	DDC/CI; Mac OS X; sRGB; Windows 10 / 8.1 / 8 / 7
Built-in camera *	✗	On/off switch	✓
Design		TV tuner integrated	✗
Market positioning *	Home	Exterior finish type	Textured
Product colour *	Black	Monitor sync input signal	Separate Sync; Sync on Green
Feet colour	Black	User controls	Power On/Off; Menu; Brightness; Input; SmartImage Game
Ports & interfaces		Picture enhancement	SmartImage game
Built-in USB hub *	✗	Signal input	VGA (Analogue); HDMI 1.4; DisplayPort 1.2
VGA (D-Sub) ports quantity	1	Regulatory Approvals	CE Mark; CU-EAC; CB; UKRAINIAN
DVI port	✗	Heavy metals free	Hg (mercury)
HDMI *	✓	LowBlue mode	✓
HDMI ports quantity	1	Compliance certificates	RoHS
HDMI version	1.4	Mean time between failures (MTBF)	50000 h
DisplayPorts quantity	1	Certification	CE Mark, CU-EAC, CB, UKRAINIAN
DisplayPort version	1.2	Recycling data	
Audio input	✗	Total amount of recyclable materials	100%
Audio output	✓	Recyclable packaging material	100%
Headphone out *	✗	Logistics data	
Ergonomics		Harmonized System (HS) code	85285210
VESA mounting *	✓		



8712581758493

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.