

ASUS ProArt PA279CV computer monitor 68.6 cm (27") 3840 x 2160 pixels 4K Ultra HD LED Black, Silver

Brand : ASUS

Product family: ProArt

Product code: 90LM06M1-B01170

Product name : PA279CV

- 27-inch 4K UHD (3840 x 2160) LED backlight display with IPS 178° wide viewing angle panel
 - International color standard 100% sRGB and 100% Rec. 709 wide color gamut
 - Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
 - Extensive connectivity including DP over USB-C™ with 65W Power Delivery, DisplayPort, HDMI, USB 3.0 hub
 - Adaptive-Sync technology (40~60Hz) to animated content with fast action and eliminate screen tearing
 - ASUS-exclusive ProArt Preset and ProArt Palette provide numerous adjustable color parameters
 - Ergonomic design with +35° ~ -5° tilt, ±45° swivel, ±90° pivot and 150mm height adjustments for a comfortable viewing experience
- 27", IPS, 4K UHD, 3840 x 2160, 5ms, 16:9, HDCP, 2 x HDMI, DisplayPort, USB Type-C, 4 x USB Type-A, 3.5mm, Flicker free, HDR-10, VESA, Frameless, 614 x 370 x 60 mm, 5.7 Kg



Display

Display diagonal *	68.6 cm (27")
Display resolution *	3840 x 2160 pixels
HD type *	4K Ultra HD
Native aspect ratio *	16:9
Display technology *	LED
Panel type *	IPS
Touchscreen *	✗
Display brightness (typical)	350 cd/m²
Response time *	5 ms
Screen shape *	Flat
Supported graphics resolutions	3840 x 2160
Aspect ratio	16:9
Contrast ratio (typical) *	1000:1
Contrast ratio (dynamic)	100000000:1
Dynamic contrast ratio marketing name	SmartContrast
Maximum refresh rate *	60 Hz
Viewing angle, horizontal	178°
Viewing angle, vertical	178°
Display number of colours *	1.073 billion colours
Pixel pitch	0.155 x 0.155 mm
Viewable size, horizontal	59.7 cm
Viewable size, vertical	33.6 cm
Viewable size diagonal	68.5 cm
Digital horizontal frequency	29 - 160 kHz
Digital vertical frequency	40 - 60 Hz
High Dynamic Range (HDR) supported	✓
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)
sRGB coverage (typical)	100%

Performance

VESA Adaptive Sync support ✓

Ports & interfaces

DisplayPort version	1.2
Audio input	✗
Headphone out *	✓
Headphone outputs	1
Headphone connectivity	3.5 mm
HDCP	✓
AC (power) in	✓

Ergonomics

VESA mounting *	✓
Panel mounting interface	100 x 100 mm
Cable lock slot *	✓
Cable lock slot type	Kensington
Height adjustment *	✓
Adjustable height (max)	15 cm
Pivot	✓
Pivot angle	-90 - 90°
Swivelling	✓
Swivel angle range	-45 - 45°
Tilt adjustment	✓
Tilt angle range	-5 - 35°


Power

Energy efficiency class (SDR) *	G
Energy efficiency class (HDR) *	G
Energy consumption (SDR) per 1000 hours *	32 kWh
Energy consumption (HDR) per 1000 hours *	54 kWh
Power consumption (typical) *	32.1 W
Power consumption (standby) *	0.5 W
Power consumption (off)	0.2 W
AC input voltage	100 - 240 V

Performance		Power	
Flicker-free technology	✓	AC input frequency	50 - 60 Hz
Low Blue Light technology	✓	Energy efficiency scale	A to G
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	614 mm
RMS rated power	2 W	Depth (with stand)	227.8 mm
Built-in speaker(s) *	✓	Height (with stand)	523.4 mm
Built-in camera *	✗	Weight (with stand)	8.6 kg
Design		Width (without stand)	614 mm
Market positioning *	Photo editing	Depth (without stand)	60 mm
Product colour *	Black, Silver	Height (without stand)	370 mm
Frameless design	✓	Weight (without stand)	5.7 kg
Front bezel colour	Black	Packaging data	
Detachable stand	✓	Package width	516 mm
Feet colour	Silver	Package depth	161 mm
Ports & interfaces		Package height	680 mm
Built-in USB hub *	✓	Package weight	11.2 kg
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package type	Box
Number of upstream ports	4	Packaging content	
USB Type-A downstream ports quantity	4	Stand included	✓
USB Type-C downstream ports quantity	1	Cables included	AC
DVI port	✗	Quick start guide	✓
HDMI *	✓	Other features	
HDMI ports quantity	2	Country of origin	China
HDMI version	2.0	Certification	TUV Flicker-free , TUV Low Blue Light, Calman Verified
DisplayPorts quantity	1	Logistics data	
		Commodity Classification Automated Tracking System (CCATS)	8528521000
		Harmonized System (HS) code	85285210



4718017853200



0192876853207



192876853207




4718017853170




0192876935248



192876935248



0192876853214



192876853214

Catalog Object Cloud



Disclaimer: The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of webpages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.