

Epson EcoTank ET-M3180 Inkjet A4 1200 x 2400 DPI 39 ppm Wi-Fi

Brand : Epson

Product family: EcoTank

Product code: C11CG93402BY

Product name : ET-M3180



- Low TCO and energy use: Keep your printing costs extremely low
- High ink yields: Print up to 11,000 pages with the included ink
- Save time: Print, scan, copy and fax
- Built for business: Duplex printing and PCL support
- Easy connectivity: Wi-Fi, USB and Ethernet

A4, Auto Duplex, 1200 x 2400DPI, Inkjet Monochrome printing, PCL5c/PCL5e/PCL6, CIS Scanner, Fax 33.6kb/s, USB, Ethernet, Wi-Fi

Epson EcoTank ET-M3180. Print technology: Inkjet, Printing: Mono printing, Maximum resolution: 1200 x 2400 DPI. Copying: Mono copying, Maximum copy resolution: 600 x 600 DPI. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI. Faxing: Colour faxing. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: White

Printing		Paper handling	
Print technology *	Inkjet	Maximum ISO A-series paper size *	A4
Printing *	Mono printing	Paper tray media types *	Envelopes, Plain paper
Duplex printing *	✓	Multi-purpose tray media types	Envelopes, Executive, Plain paper
Maximum resolution *	1200 x 2400 DPI	ISO A-series sizes (A0...A9) *	A4, A5, A6
Print speed (black, normal quality, A4/US Letter) *	39 ppm	ISO B-series sizes (B0...B9)	B5, B6
Duplex print speed (black, normal quality, A4/US Letter)	9 ppm	Non-ISO print media sizes	Executive, Legal, Letter
Time to first page (black, normal)	6 s	Envelopes sizes	10, C6, DL
Copying		Paper tray media weight	64 - 256 g/m ²
Copying *	Mono copying	Ports & interfaces	
Maximum copy resolution *	600 x 600 DPI	Direct printing *	✓
Maximum number of copies	99 copies	USB port	✓
Copier resize	25 - 400%	Network	
Scanning		Wi-Fi *	✓
Scanning *	Colour scanning	Ethernet LAN *	✓
Optical scanning resolution *	1200 x 2400 DPI	Security algorithms	64-bit WEP, 128-bit WEP, WPA-AES, WPA-PSK, WPA-TKIP
Scan technology	CIS	Mobile printing technologies	Apple AirPrint, Epson Connect, Epson Email Print, Epson Remote Print, Epson iPrint, Google Cloud Print
Scan to	Cloud		
Scan speed (black)	7 inch/min	Performance	
Scan speed (colour)	7 inch/min	Internal memory *	2 MB
Image formats supported	BMP, JPEG, PNG, TIFF	Design	
Document formats supported	PDF	Product colour *	White
Fax		Market positioning *	Home & office
Faxing *	Colour faxing	Built-in display *	✓
Fax transmission speed	3 sec/page	Display	LCD
Modem speed	33.6 Kbit/s	Display diagonal	6.1 cm (2.4")
Fax memory	180 pages	Touchscreen	✓
Auto-redialing	✓	Control type	Touch
Speed dialling	✓	Colour display	✓
Fax speed dialling (max numbers)	100	Power	
Fax forwarding	✓	Power consumption (printing)	14 W
Fax forwarding to	PC	Power consumption (copying)	12 W
Error Correction Mode (ECM)	✓	Energy Star Typical Electricity Consumption (TEC)	0.2 kWh/week
Features		AC input voltage	220 - 240 V
Recommended duty cycle	250 - 1500 pages per month		
Maximum duty cycle *	20000 pages per month		

Features		System requirements	
Page description languages	PCL 5c, PCL 5e, PCL 6	Windows operating systems supported	✓
Input & output capacity		Mac operating systems supported	✓
Total number of input trays *	2	Server operating systems supported	Windows Server 2008, Windows Server 2008 R2, Windows Server 2008 x64, Windows Server 2012 R2, Windows Server 2012 x64, Windows Server 2016
Total input capacity *	251 sheets		
Total output capacity *	100 sheets		
Paper input type	Paper tray		
Auto document feeder (ADF)	✓		
Auto document feeder (ADF) input capacity	35 sheets	Sustainability	
Maximum input capacity	251 sheets	Sustainability certificates	ENERGY STAR
Weight & dimensions			
		Width	375 mm
		Depth	347 mm
		Height	346 mm
		Weight	7.3 kg
Packaging content			
		Warranty card	✓
Logistics data			
		Harmonized System (HS) code	84433100



8715946655222

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.