

Technical datasheet: FT-35G-3.2B1-476

Specifications:

Resonant Frequency	3.2kHz \pm 0.5kHz
Max Resistance (Zr)	300 Ω
Capacitance	26000nF \pm 30%nF

Dimensions:

Type B: (D: \varnothing 35mm, d: \varnothing 25mm, T: 0.55mm, t: 0.30mm)

