


Technical datasheet: KPCM-G45H22PC33-44DB-1175

Specifications:

| | |
|----------------------------|---------------------|
| Standard operation voltage | 2VDC |
| Max operating voltage | 10VDC |
| Output impedance | 2.2k Ω |
| Frequency | 100 Hz to 10,000 Hz |
| Sensitivity | -44dB \pm 3dB |
| Sensitivity reduction | -3dB |
| Max. Current Consumption | 0.5mA |
| Signal to noise ration | 60dB |
| Directivity | Omni-directional |

Dimensions:



Frequency Response:

