


Technical datasheet: KPI-G2313-K6256

Specifications:

Operating Temperature	-20°C to +80°C
Storage Temperature	-30°C to +100°C
Rated Voltage	12VDC
Operating Voltage	8VDC to 15VDC
Max. Rated Current	15mA at 12VDC
Resonant Frequency	3.3kHz \pm 0.5kHz
Min SPL	88dB / 12VDC / 30cm
Weight	8g
Case Material/Color	PC/Black
Tone Nature	Continuous

Dimensions:



Frequency Response:

