


Technical datasheet: KPX-G0905B-K6334

Specifications:

Operating Temperature	-20°C to +70°C
Storage Temperature	-30°C to +80°C
Rated Voltage	5VDC
Operating Voltage	4VDC to 8VDC
Max. Rated Current	30mA at 5VDC
Resonant Frequency	2.7kHz±0.3kHz
Min SPL	80dB/ 5VDC/ 10cm
Weight	1g
Case Material/Color	PBT/Black
Tone Nature	Continuous

Dimensions:



Frequency Response:

