

Technical datasheet: FT-10.5T-9.0A1-462

Specifications:

Resonant Frequency	8.5kHz \pm 0.5kHz
Max Resistance (Zr)	700 Ω
Capacitance	9000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 10.5mm, d: \varnothing 7.5mm, T: 0.14mm, t: 0.07mm)

