


Technical datasheet: KPMB-3008E-6106

Specifications:

Operating Temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Rated Voltage	1.1Vrms sine Wave
Max Allowable Voltage	1.55Vrms sine Wave
Min SPL	85dB at 0.1W/0.1M at 1kHz
Resonance Frequency	1.1KHz±20%
Weight	10g
Case Material/Color	ABS/Black
Tone Nature	Continues

Dimensions:



Frequency Response:

