



HP Color LaserJet Enterprise M751dn

Brand : HP

Product family: Color LaserJet Enterprise

Product code: T3U44A#B19

Product name : Color LaserJet Enterprise M751dn

- Two-sided printing
 - Print
 - Print speed up to 40 ppm (black) and 40 ppm (color)
 - Up to 1200 x 1200 dpi
- Color LaserJet Enterprise M751dn

[HP Color LaserJet Enterprise M751dn:](#)

HP LaserJet printers power office productivity with a smart, streamlined design that's reliable and hassle-free. Count on premium quality, maximum uptime, and the strongest security^[1] – all intended to drive successful organizations forward.

Dynamic security enabled printer Certain HP printers are intended to work only with cartridges that have a new or reused HP chip or electronic circuitry. These printers use dynamic security measures to block cartridges using a non-HP chip or electronic circuitry. Periodic firmware updates will maintain the effectiveness of these measures and block cartridges that previously worked. Reused HP chips and electronic circuitry enable the use of reused, remanufactured, and refilled cartridges.



Printing		Design				
Duplex printing mode	Auto	Certification	CISPR 22:2008 (International) - Class A, CISPR32:2012 (International) - Class A, EN 55032:2012 (EU) - Class A, EN 61000-3-2:2014, EN 61000-3-3:2013, EN 55024:2010, EMC Directive 2014/30/EU, Issue 6 Class A, other EMC approvals as required by individual countries.			
Print resolution colour	1200 x 1200 DPI					
Print resolution black	1200 x 1200 DPI					
Print speed (colour, normal quality, A4/US Letter)	41 ppm					
Colour *	✓					
Print technology *	Laser					
Duplex printing *	✓					
Maximum resolution *	1200 x 1200 DPI					
Print speed (black, normal quality, A4/US Letter) *	41 ppm	Power	Power consumption (printing) *	870 W		
Print speed (colour, draft quality, A4/US Letter)	41 ppm		Power consumption (max)	870 W		
Print speed (black, normal quality, A3)	26 ppm		Power consumption (ready)	48 W		
Print speed (colour, normal quality, A3)	26 ppm		Power consumption (PowerSave)	0.6 W		
Warm-up time	131 s		Power consumption (off)	0.08 W		
Time to first page (black, normal)	5.7 s		Energy Star Typical Electricity Consumption (TEC)	1.93 kWh/week		
Time to first page (colour, normal)	6.1 s		AC input voltage	220 - 240 V		
Print margins (top, bottom, right, left)	5 mm		AC input frequency	50/60 Hz		
Watermark printing	✓		System requirements	Windows operating systems supported	Windows 7 Enterprise, Windows 7 Ultimate, Windows 7 Professional, Windows 7 Starter, Windows 7, Windows 8 Pro, Windows 8 Enterprise, Windows 8, Windows 8.1 Pro, Windows 8.1 Enterprise, Windows 8.1, Windows 10 Pro, Windows 10 Enterprise, Windows 10	
Secure printing	✓					
Features						
Maximum duty cycle *	150000 pages per month	Mac operating systems supported	Other operating systems supported	Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, MacOS		
Recommended duty cycle	0 - 40000 pages per month					
Printing colours *	Black, Cyan, Magenta, Yellow					
Number of print cartridges *	4	Operational conditions	Operating temperature (T-T)	10 - 32.5 °C		
Page description languages *	PostScript 3, PDF 1.7, PCL 6				Storage temperature (T-T)	-20 - 40 °C
Printer fonts	Scalable, TrueType, Windows, PCL, PostScript					
Country of origin	Japan					

Features		Sustainability	
Replacement cartridges	HP 658A Black LaserJet Toner Cartridge (7,000 pages); HP 658A Cyan LaserJet Toner Cartridge (6,000 pages); HP 658A Magenta LaserJet Toner Cartridge (6,000 pages); HP 658A Yellow LaserJet Toner Cartridge (6,000 pages); HP 658X Black LaserJet Toner Cartridge (33,000 pages); HP 658X Cyan LaserJet Toner Cartridge (28,000 pages); HP 658X Magenta LaserJet Toner Cartridge (28,000 pages); HP 658X Yellow LaserJet Toner Cartridge (28,000 pages); HP 660A Original LaserJet Imaging Drum (65,000 pages, universal for all 4 colours)	Sustainability compliance	✓
		Sustainability certificates	ENERGY STAR, Blue Angel, EPEAT Silver
		Sustainable technologies and materials	Mercury free
		Doesn't contain	Mercury
HP segment	Business	Carbon footprint	
Input & output capacity	Total number of input trays * Total input capacity * Total output capacity * Paper tray 1 input capacity Paper tray 2 input capacity Paper input type Multi-Purpose tray Multi-Purpose tray input capacity Maximum number of input trays Maximum input capacity Maximum output capacity	Total carbon footprint (kg of CO2e)	710
		Carbon emissions, manufacturing (kg of CO2e)	449
		Carbon emissions, logistics (kg of CO2e)	59
		Total carbon emissions, w/o use phase (kg of CO2e)	185
		Weight & dimensions	
		Width	556 mm
		Depth	589 mm
		Height	399 mm
		Pallet dimensions (W x D x H)	790 x 760 x 2359 mm
		Weight	45.1 kg
Packaging data	Package width Package depth Package height Package weight	786 mm	
		736 mm	
		558 mm	
		52.9 kg	
		Packaging content	
Paper handling	Maximum ISO A-series paper size * Maximum print size Paper tray media types * ISO A-series sizes (A0...A9) * ISO B-series sizes (B0...B9) ISO C-series sizes (C0...C9) Non-ISO print media sizes JIS B-series sizes (B0...B9) Envelopes sizes Custom media width Custom media length Paper tray media weight Multi-Purpose Tray media weight	Cables included	AC
		Brand-specific features	
		HP ePrint	✓
		HP SureSupply	✓
		HP Auto-On/Auto-Off	✓
		HP Dynamic security	✓
		HP Security tools	Management security: SNMPv3, SSL/TLS, WPA2-Enterprise, 802.1X authentication (EAP- PEAP, EAP-TLS), IPP over TLS, IPsec/Firewall with Certificate, Pre-Shared Key Authentication, and Kerberos Authentication; Support for WJA-10 IPsec Configuration using IPsec Plug-in
		HP Software provided	; Apple AirPrint™; Mopria™ Certified; Google Cloud Print™; HP Roam
		HP GTIN (EAN/UPC) with options	(ABT) 192018847972; (ABY) 192018847989; (ACQ) 192018847996; (B13) 192018848009; (B19) 192018848016; (BAZ) 192018848023
		HP GTIN (EAN/UPC)	192018847972, 192018847989, 192018847996, 192018848009, 192018848016, 192018848023
		Logistics data	
		Harmonized System (HS) code	84433210
		Pallet gross weight	221.5 kg
		Layers per pallet	4 pc(s)
		Products per pallet	4 pc(s)
Technical details			
Master (outer) cases per pallet layer 1 pc(s) Compliance certificates CECF General Product Safety Regulation https://support.hp.com/gb-en/product/setup-user-guides/hp-color-laserjet-enterprise-m751-printer-series/model/19954834?sku=T3U44A&serialnumber=T3U44A GPSR URL https://h10322.www1.hp.com/cgi-bin/Manuals/06286726.pdf			

Network		Other features	
Security algorithms	SNMPv3, SSL/TLS, WPA2-Enterprise, EAP-PEAP, EAP-TLS	Recommended system requirements	2 GB available hard disk space; Internet connection; USB port; Internet browser. 2 GB available hard disk space; Internet connection or USB port.
Supported network protocols (IPv4)	Auto-IP, SLP, Telnet, IGMPv2, BOOTP/DHCP, WINS, IP Direct Mode, WS Print		
Supported network protocols (IPv6)	Apple Bonjour Compatible (Mac OS v10.2.4 or higher), SNMPv1/v2c/v3, HTTP, HTTPS, FTP, TFTP, Port 9100, LPD, WS Discovery, IPP, Secure-IPP, IPsec/Firewall; IPv6: DHCPv6, MLDv1, ICMPv6	Recommended humidity operating range	30 - 70%
		Recommended operating temperature range (T-T)	15 - 27 °C
Mobile printing technologies	Mopria Print Service, HP ePrint, Apple AirPrint, Google Cloud Print	Custom media sizes	100 sheet multipurpose tray 1: 64 x 127 to 320 x 457.2 mm; 550 sheet input tray 2: 148 x 148 to 297 x 431.8 mm; Optional 1 x 550 and 2 x 550 tray and stand: 148 x 148 to 320 x 457.2 mm; Optional 2,700 sheet HCL paper tray and stand: 279.4 x 210 to 297 x 215.9 mm
Performance			
Internal memory *	1536 MB	Envelope feeder	No
Maximum internal memory	3584 MB		
Memory slots	1	Electromagnetic compatibility	CISPR 22:2008 (International) - Class A, CISPR32:2012 (International) - Class A, EN 55032:2012 (EU) - Class A, EN 61000-3-2:2014, EN 61000-3-3:2013, EN 55024:2010, EMC Directive 2014/30/EU, Issue 6 Class A, other EMC approvals as required by individual countries.
Memory type	DDR3		
Internal storage capacity	500 GB	Compatible operating systems	Windows Client OS (32/64-bit), Windows 10, Windows 8.1, Windows 8 Basic, Windows 8 Pro, Windows 8 Enterprise, Windows 8 Enterprise N, Windows 7 Starter Edition SP1, UPD Windows 7 Ultimate, Mobile OS, iOS, Android, Mac, Apple macOS Sierra v10.12, Apple macOS High Sierra v10.13, Apple macOS Mojave v10.14, Discrete PCL6 Printer Driver, for more information on the supported operating systems go to http://www.support.hp.com , enter your product name and search, click on User Guides and enter your product name and search for User Guide, search for your (Product Name) - User Guide, search for the Supported Operating Systems section, UPD PCL6 / PS Printer Drivers, Supported Operating systems, for more information on the supported operating systems see http://www.hp.com/go/upd
Storage media	HDD		
Card reader integrated	✗	Pallet dimensions (W x D x H) (imperial)	789.9 x 760 x 2359.7 mm (31.1 x 29.9 x 92.9")
Built-in processor	✓		
Processor frequency	1200 MHz	Pallet weight (imperial)	221.5 kg (488.4 lbs)
Coprocessor frequency	1.2 GHz		
Sound pressure level (printing)	51 dB	Acoustic power emissions (ready)	45 dB
Noise level (ready)	30 dB		
Sound power level (printing)	6.6 dB	Acoustic pressure emissions bystander (ready)	30 dB
Design			
Market positioning *	Business	Typical electricity consumption (TEC) number	Blue Angel: 1.93 kWh/Week; Energy Star 3.0: 0.551 kWh/Week
Product colour *	White		
Built-in display *	✓	UNSPSC-code	43212105
Display	LCD		
Colour display	✓	Box contents	HP Color LaserJet Enterprise M751dn printer; Four preinstalled HP LaserJet Toner cartridges (1 each, black, cyan, yellow, magenta); Four preinstalled HP Original LaserJet Imaging Drums (65,000 pages each colour); Getting started guide; Power cord
Display diagonal	6.86 cm (2.7")		
Control type	Buttons	Printing	Colour printing
		Processor frequency	1.2 GHz
		Manufacturer warranty	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements.



0192018848016



192018848016

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.