

Epson EH-TW7000 Standard throw projector 3000 ANSI lumens 3LCD 3D White



Brand : Epson

Product code: V11H961041

Product name : EH-TW7000

- 4K PRO-UHD for crisp, clear images: Watch native 4K and upscale non-4K content
- Easy to set up and access content: Stream content by plugging devices into either of the two HDMI ports

- High-quality and affordable: Flexible features that deliver a 4K experience at an affordable price

- Engaging big-screen experience: Get the best out of movies, sports and gaming

- Watch a movie a day for the next 7 years: 5,000 hours lamp life in Eco mode

EH-TW7000, 3LCD, 3000 lum, 4K PRO-UHD, 16:9, USB 2.0, HDMI, Bluetooth, AC 100-240 V, 410x310x157 mm

Projector		Storage	
Screen size compatibility *	1016 - 12700 mm (40 - 500")	Card reader integrated *	×
Projection distance	2.95 - 4.77 m	Features	
Projector brightness *	3000 ANSI lumens	Noise level (economic mode)	24 dB
Projection technology *	3LCD	Noise level *	32 dB
Contrast ratio (typical) *	40000:1	Country of origin	Philippines
Native aspect ratio *	16:9	Multimedia	
Number of colours	1.073 billion colours	Built-in speaker(s) *	×
Keystone correction, horizontal	-30 - 30°	Design	
Keystone correction, vertical	-30 - 30°	Market positioning *	Home cinema
Matrix size	1.55 cm (0.61")	Product type *	Standard throw projector
Light source		Product colour *	White
Light source type *	Lamp	Placement	Desktop, Ceiling
Service life of light source *	3500 h	Display	
Service life of light source (economic mode)	5000 h	Built-in display *	×
Lamp type	UHE	Power	
Lamp power	250 W	Power source *	AC
Lamps quantity	1 lamp(s)	Power consumption (typical) *	368 W
Lens system		Power consumption (standby) *	0.5 W
Focus *	Manual	Power consumption (economy mode)	280 W
Focal length range	18.2 - 29.2 mm	AC input voltage	100 - 240 V
Aperture range (F-F)	1.49 - 1.77	AC input frequency	50 - 60 Hz
Zoom capability	✓	Operational conditions	
Zoom type	Manual	Operating temperature (T-T)	5 - 30 °C
Zoom ratio	1:1.62	Storage temperature (T-T)	-10 - 60 °C
Throw ratio	1.32 - 2.15:1	Operating relative humidity (H-H)	20 - 80%
Horizontal lens shift range	-24 - 24%	Storage relative humidity (H-H)	10 - 90%
Vertical lens shift range	-60 - 60%	Weight & dimensions	
Video		Width	410 mm
Full HD *	✓	Depth	310 mm
3D *	✓	Height	157 mm
Supported 3D formats	Side by side, Top and bottom	Weight *	6.6 kg
Video colour modes	Auto, Bright cinema, Cinema, Dynamic, Natural	Package width	495 mm
Ports & interfaces		Package depth	495 mm
HDMI connector type	Full-size	Package height	230 mm
USB 2.0 ports quantity	2	Package weight	8.71 kg
Mini-USB 2.0 ports quantity	1		

Ports & interfaces		Packaging content	
Serial interface type *	RS-232C	Remote control included *	✓
PC Audio out	✓	Cables included	AC
HDMI ports quantity *	2	Manual	✓
DVI port *	✗	Logistics data	
AC (power) in	✓	Quantity per pack	1 pc(s)
Network		Products per pallet	18 pc(s)
Smart TV *	✗	Products per pallet layer	2 pc(s)
Ethernet LAN *	✗	Products per pallet layer (UK)	4 pc(s)
Wi-Fi *	✗	Products per pallet (UK)	36 pc(s)
Bluetooth	✓	Harmonized System (HS) code	85286200



8715946670874

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.