



Canon CLI-42GY Grey Ink Cartridge

Brand : Canon

Product code: 6390B001

Product name : CLI-42GY Grey Ink Cartridge

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges²
 - Genuine Canon Ink provides consistent quality prints 100% of the time²
 - Genuine Canon Ink is 100% reliable so you can print with less stress²
 - Return every toner ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- CLI-42GY Grey Ink Cartridge

[Canon CLI-42GY Grey Ink Cartridge:](#)

The ChromaLife100+ dye-based ink range delivers stunning quality and vibrant photos in colour and monochrome. The 13ml grey ink tank allows you to print up to 492 photos in 10x15cm or 70 in A3+ size at ISO/IEC 24711¹ standard.

Canon CLI-42GY Grey Ink Cartridge. Colour ink type: Pigment-based ink, Cartridge capacity: Standard Yield, Colour ink page yield: 492 pages, Printing colours: Grey, Quantity per pack: 1 pc(s)

Features		Operational conditions	
Colour ink type	Pigment-based ink	Operating relative humidity (H-H)	5 - 95%
Print technology	Inkjet printing	Storage temperature (T-T)	10 - 35 °C
Compatibility *	Canon PIXMA PRO-100	Operating temperature (T-T)	15 - 35 °C
Quantity per pack *	1 pc(s)	Storage relative humidity (H-H)	5 - 95%
Colour ink page yield *	492 pages	Packaging data	
Type *	Original	Package type	Blister
Cartridge capacity	Standard Yield	Other features	
Ink type	Pigment-based ink	Page yield footnote	10x15cm, ISO/IEC 24734
Printing colours *	Grey	Logistics data	
Country of origin	Japan	Harmonized System (HS) code	84439990
Colour	×		





4960999901886

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.