

## dbramante1928 Greenland - iPhone 12/12 Pro - Pacific Blue

**Brand :** dbramante1928

**Product code:** GL61PABL1278

**Product name :** Greenland - iPhone 12/12 Pro - Pacific Blue

- Guided by WWF, dbramante1928 is becoming a Climate Positive Company
  - Made from 100% recycled plastic
  - The equivalent recycled material weight of a 2L plastic bottle is used to make each case
  - Slim, impact protection case with non-slip grip and easy-to-press buttons
  - Compatible with wireless charging in case
  - Raised edges protect camera and screen
- Greenland - iPhone 12/12 Pro - Pacific Blue

[dbramante1928 Greenland - iPhone 12/12 Pro - Pacific Blue:](#)

Made from 100% recycled plastic, protect your phone and the planet at the same time with this all-around, slim, snap-on impact protection case. Designed in Denmark by a Climate Positive Company, and eco-friendly without compromising quality, protection, design or functionality, this case feels great in your hand. It is ideal for those looking to bring effortless style to their everyday lives.



| Features                  |                  | Packaging data                             |                          |
|---------------------------|------------------|--------------------------------------------|--------------------------|
| Maximum screen size *     | 15.5 cm (6.1")   | Package weight                             | 86 g                     |
| Surface coloration        | Monochromatic    | Logistics data                             |                          |
| Compatibility *           | iPhone 12/12 Pro | Harmonized System (HS) code                | 85177900                 |
| Case type *               | Cover            | Country of origin                          | China                    |
| Material *                | Recycled plastic | Shipping (inner) case net weight           | 59 g                     |
| Product colour *          | Blue             | Shipping (inner) case gross weight         | 86 g                     |
| Brand compatibility *     | Apple            | Quantity outer carton                      | 30 pc(s)                 |
| Weight & dimensions       |                  | Master (outer) case width                  | 395 mm                   |
| Width                     | 76 mm            | Master (outer) case length                 | 245 mm                   |
| Depth                     | 11 mm            | Master (outer) case height                 | 230 mm                   |
| Height                    | 150 mm           | Master (outer) case net weight             | 740 g                    |
| Weight                    | 27 g             | Master (outer) case gross weight           | 740 g                    |
| Packaging content         |                  | Master (outer) case volume                 | 22258.25 cm <sup>3</sup> |
| Quantity per pack         | 30 pc(s)         | Master (outer) cases per pallet layer (EU) | 48 pc(s)                 |
| Sustainability            |                  | Products per pallet (EU)                   | 1440 pc(s)               |
| Sustainability compliance | ✓                | Pallet gross weight                        | 3.71 kg                  |
| Packaging data            |                  |                                            |                          |
| Package width             | 117 mm           |                                            |                          |
| Package depth             | 20 mm            |                                            |                          |
| Package height            | 207 mm           |                                            |                          |



5711428012784

### **Catalog Object Cloud**



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.