

ZYXEL

Zyxel MG-105 Unmanaged 2.5G Ethernet (100/1000/2500) Steel

Brand : Zyxel

Product code: MG-105-ZZ0101F

Product name : MG-105

- Support 2.5GbE on all ports
- Instantly upgrade speed up to 2.5 times
- Increase home networking speed without extra cabling cost
- Access Internet just plug-and-play
- Silent and stable operation

25 Gbps, 18.6 Mpps, 5x 2.5 RJ-45, QoS, 100-240V AC, 50/60 Hz, 160x110x26 mm

Zyxel MG-105. Switch type: Unmanaged. Basic switching RJ-45 Ethernet ports type: 2.5G Ethernet (100/1000/2500), Basic switching RJ-45 Ethernet ports quantity: 5. Full duplex. MAC address table: 16000 entries, Switching capacity: 25 Gbit/s. Networking standards: IEEE 802.1p, IEEE 802.3, IEEE 802.3ab, IEEE 802.3bz, IEEE 802.3u, IEEE 802.3x. Wall mountable



Management features		Power	
Switch type *	Unmanaged	Power supply included *	✓
Quality of Service (QoS) support	✓	AC input voltage	100 - 240 V
Ports & interfaces		AC input frequency	50 - 60 Hz
Basic switching RJ-45 Ethernet ports quantity *	5	Power consumption (max)	9.34 W
Basic switching RJ-45 Ethernet ports type *	2.5G Ethernet (100/1000/2500)	Power over Ethernet (PoE)	
Network		Power over Ethernet (PoE) *	✗
Networking standards *	IEEE 802.1p, IEEE 802.3, IEEE 802.3ab, IEEE 802.3bz, IEEE 802.3u, IEEE 802.3x	Operational conditions	
10G support *	✗	Operating temperature (T-T)	0 - 40 °C
Copper ethernet cabling technology	2.5GBASE-T, 100BASE-TX, 1000BASE-T	Storage temperature (T-T)	-40 - 70 °C
Full duplex	✓	Operating relative humidity (H-H)	10 - 90%
Flow control support	✓	Storage relative humidity (H-H)	5 - 95%
Auto MDI/MDI-X	✓	Weight & dimensions	
Auto-negotiation	✓	Width	160 mm
Data transmission		Depth	110 mm
Switching capacity *	25 Gbit/s	Height	26 mm
Forwarding rate	18.6 Mpps	Weight	460 g
MAC address table *	16000 entries	Packaging content	
Jumbo frames support	✓	User guide	✓
Jumbo frames	12000	Packaging data	
Packet buffer memory	12 MB	Package width	215 mm
Design		Package depth	133 mm
Rack mounting *	✗	Package height	79 mm
		Package weight	919.6 g
		Certificates	
		Compliance certificates	CE
		Certification	CE, EAC, FCC, BSMI

Design		Logistics data	
Product colour	Steel	Harmonized System (HS) code	85176990
LED indicators	✓		
Wall mountable	✓		
Performance			
Fanless	✓		



4718937620203



0760559127855



760559127855

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.