

Epson EB-PU2010W Large venue projector 10000 ANSI lumens 3LCD WUXGA (1920x1200) White

Brand : Epson

Product code: V11HA52940

Product name : EB-PU2010W

3LCD, 1.03" with C2 Fine, WUXGA, 1920 x 1200, 16:10, 10000 Lumen

Epson EB-PU2010W. Projector brightness: 10000 ANSI lumens, Projection technology: 3LCD, Projector native resolution: WUXGA (1920x1200). Light source type: Laser, Service life of light source: 20000 h, Service life of light source (economic mode): 30000 h. Focal length range: varies by lens, Zoom type: Auto, Throw ratio: 0.35 - 7.41:1. Video processing: 10 bit, Video colour modes: Cinema, Dynamic, Natural, Presentation, DICOM simulation mode, Multi-projection, BT.709. Serial interface type: RS-232C



Projector		Design	
Projector brightness *	10000 ANSI lumens	Market positioning *	Business
Projection technology *	3LCD	Product type *	Large venue projector
Projector native resolution *	WUXGA (1920x1200)	Product colour *	White
Contrast ratio (typical) *	2000:1	Placement	Ceiling, Desktop, Flying frame
Native aspect ratio *	16:10	Cable lock slot	✓
Number of colours	1.07 billion colours	Cable lock slot type	Kensington
Projector brightness (economic mode)	7000 ANSI lumens	Display	
Projector brightness (portrait mode)	10000 ANSI lumens	Built-in display *	✗
Keystone correction, horizontal	-30 - 30°	Power	
Keystone correction, vertical	-45 - 45°	Power source *	AC
Matrix size	2.62 cm (1.03")	Power consumption (typical) *	535 W
Heat dissipation	1819 BTU/h	Power consumption (standby) *	0.5 W
Light source		Power consumption (economy mode)	452 W
Light source type *	Laser	AC input voltage	100-240 V
Service life of light source *	20000 h	AC input frequency	50 - 60 Hz
Service life of light source (economic mode)	30000 h	Software	
Lens system		Software support	via: Crestron Integrated Partner, Extron IP Link, Extron XTP, AMX Device Discovery
Focal length range	varies by lens	Operational conditions	
Zoom type	Auto	Storage temperature (T-T)	-10 - 60 °C
Throw ratio	0.35 - 7.41:1	Operating relative humidity (H-H)	20 - 80%
Interchangeable lens	✓	Storage relative humidity (H-H)	10 - 90%
Video		Weight & dimensions	
Analog signal format system *	Not supported	Width	545 mm
Full HD *	✓	Depth	436 mm
3D *	✗	Height	189 mm
Video processing	10 bit	Weight *	16.8 kg
Video colour modes	Cinema, Dynamic, Natural, Presentation, DICOM simulation mode, Multi-projection, BT.709	Package width	570 mm
Ports & interfaces		Package depth	765 mm
USB 2.0 Type-B ports quantity	1	Package height	270 mm
Audio (L/R) in *	1	Package weight	22.1 kg
Serial interface type *	RS-232C		

Ports & interfaces		Packaging content	
VGA (D-Sub) ports quantity *	1	Remote control included *	✓
HDMI ports quantity *	1	Batteries included	✓
DVI port *	✓	Cables included	AC
Network		Manual	✓
Ethernet LAN *	✓	Warranty card	✓
Ethernet LAN (RJ-45) ports	1	WLAN adapter included	✓
Storage		Bundled software	Inhalt DIY-App, EasyMP Multi PC Projection, Epson Projektor Content Manager, Epson Projektor Management, Epson Projektor Professional Tool
Card reader integrated *	✗		
Features		Logistics data	
Noise level (economic mode)	30 dB	Quantity per pack	1 pc(s)
Preset modes	Cinema, Dynamic, Presentation	Products per pallet	14 pc(s)
Noise level *	37 dB	Pallet gross weight	0 g
Country of origin	Philippines	Products per pallet (UK)	14 pc(s)
Password protection	✓	Pallet weight (UK)	0 g
		Harmonized System (HS) code	85286200
		Other features	
		Supported network protocols	HTTPS, IPv6, SNMP, ESC/VP.net, PJLink



8715946697451

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.