

Philips 242B1TC/00 computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Touchscreen Black

Brand : Philips

Product code: 242B1TC/00

Product name : 242B1TC/00

242B1TC LCD monitor with SmoothTouch

Philips 242B1TC/00 computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Touchscreen Black:

A durable, anti-glare touchscreen for flexible use, with articulating stand to angle as you need. Advanced In-Cell Touch (AIT) offers a slimmer look, superior touch sensitivity for quick response, outstanding and clearer visibility.

Philips 242B1TC/00. Display diagonal: 60.5 cm (23.8"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	60.5 cm (23.8")	Cable lock slot *	✓
Display resolution *	1920 x 1080 pixels	Cable lock slot type	Kensington
HD type *	Full HD	Height adjustment *	✓
Native aspect ratio *	16:9	Adjustable height (max)	8 cm
Display technology *	LED	Tilt angle range	-5 - 90°
Panel type *	IPS	On Screen Display (OSD)	✓
Backlight type	W-LED	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Touchscreen *	✓		
Touchscreen technology	Capacitive		
Touch technology	Multi-touch	Number of OSD languages	21
Number of simultaneous touchpoints	10	Palm rejection area	30 x 30 mm
Display brightness (typical)	250 cd/m²	Plug and Play	✓
Display brightness	250 cd/m²	LED indicators	Operation, Stand-by
Response time *	4 ms	Power	
Screen shape *	Flat	Energy efficiency class (SDR) *	E
Aspect ratio	16:9	Energy consumption (SDR) per 1000 hours *	18 kWh
Contrast ratio (typical) *	1000:1	Power consumption (typical) *	15.6 W
Contrast ratio (dynamic)	50000000:1	Power consumption (standby) *	0.3 W
Dynamic contrast ratio marketing name	SmartContrast	Power consumption (off)	0 W
Maximum refresh rate *	75 Hz	Power consumption (PowerSave)	9.8 W
Viewing angle, horizontal	178°	AC input voltage	100 - 240 V
Viewing angle, vertical	178°	AC input frequency	50 - 60 Hz
Display number of colours *	16.7 million colours	Power supply type	Internal
Pixel pitch	0.2745 x 0.2745 mm	Operational conditions	
Pixel density	93 ppi	Operating temperature (T-T)	0 - 40 °C
Horizontal scan range	30 - 85 kHz		
Vertical scan range	48 - 75 Hz		
Viewable size, horizontal	52.7 cm		

Display		Operational conditions	
Viewable size, vertical	29.6 cm	Storage temperature (T-T)	-20 - 60 °C
Display diagonal (metric)	60.5 cm	Operating relative humidity (H-H)	20 - 80%
DDC/CI	✓	Operating altitude	0 - 3658 m
Surface hardness	3H	Non-operating altitude	0 - 12192 m
sRGB coverage (typical)	102%	Weight & dimensions	
NTSC coverage (typical)	88%	Width (with stand)	540 mm
Adobe RGB coverage	83%	Depth (with stand)	227 mm
Display sRGB	✓	Height (with stand)	403 mm
Performance		Weight (with stand)	6.67 kg
NVIDIA G-SYNC *	✗	Width (without stand)	540 mm
AMD FreeSync *	✗	Depth (without stand)	51 mm
Component video sync	Separate Sync, Sync-on-green (SOG)	Height (without stand)	323 mm
Flicker-free technology	✓	Weight (without stand)	3.34 kg
Low Blue Light technology	✓	Packaging data	
Windows operating systems supported	Windows 10	Package width	620 mm
Multimedia		Package depth	140 mm
Number of speakers	2	Package height	420 mm
RMS rated power	2 W	Package weight	9.01 kg
Built-in speaker(s) *	✓	Packaging content	
Built-in camera *	✗	Stand included	✓
Design		Cables included	HDMI, DisplayPort, USB Type-A to USB Type-B, AC
Market positioning *	Home	Manual	✓
Product colour *	Black	Bundled software	SmartControl
Front bezel colour	Black	Sustainability	
Feet colour	Black	Sustainability certificates	ENERGY STAR, TCO
Ports & interfaces		Doesn't contain	PVC/BFR, Mercury
Built-in USB hub *	✗	Other features	
Number of upstream ports	1	Exterior finish type	Textured
Number of USB Type-C upstream ports quantity	1	Display viewable area (HxV)	527.04 x 296.46 mm
USB Type-A downstream ports quantity	3	Picture enhancement	SmartImage
USB Touch port	✓	Regulatory Approvals	UKRAINIAN; CB; SEMKO; TUV/GS; TUV Ergo; CU-EAC; EAEU RoHS; CE Mark; ICES-003; FCC Class B; TUV Eye Comfort certified
VGA (D-Sub) ports quantity	1	Heavy metals free	Hg (mercury)
HDMI *	✓	Folding angle	70°
HDMI ports quantity	1	Touch method	Finger
HDMI version	1.4	EasyRead mode	✓
DisplayPorts quantity	1	Energy efficiency class (old)	E
DisplayPort version	1.2	Compliance certificates	RoHS
Headphone out *	✓	Mean time between failures (MTBF)	70000 h
PC Audio in	✓	Certification	UKRAINIAN, CB, SEMKO, TUV/GS, TUV Ergo, CU-EAC, EAEU RoHS, CE Mark, ICES-003, FCC Class B, TUV Eye Comfort certified
Ergonomics		Recycling data	
VESA mounting *	✓	Recyclable packaging material	100%
Panel mounting interface	100 x 100 mm	Logistics data	
		Harmonized System (HS) code	85285210



8712581772352

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.