



Lenovo 4XC7A08237 network card Internal Fiber 25000 Mbit/s

Brand : Lenovo

Product code: 4XC7A08237

Product name : 4XC7A08237



ThinkSystem Broadcom 57414 10/25GbE SFP28 2-port OCP Ethernet Adapter

Lenovo 4XC7A08237 network card Internal Fiber 25000 Mbit/s:

The ThinkSystem Broadcom 57412 and 57414 10/25GbE SFP28 Ethernet Adapters are high-performance 25 Gb Ethernet adapters that offers TruFlow intelligent flow processing and support advanced networking technologies including RoCE, SDN, NFV and virtualization. Both 1-port (57412) and 2-port (57414) adapters are offered.

- One Broadcom adapter
 - An attached full-height (3U) bracket, and a low-profile (2U) bracket that can be substituted if needed
 - Documentation flyer
- Lenovo 4XC7A08237. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Fiber. Maximum data transfer rate: 25000 Mbit/s. Product colour: Black, Green, Stainless steel

Ports & interfaces		Design	
Connectivity technology *	Wired	Compatible products	SR635 V3 (7D9H / 7D9G) SR655 V3 (7D9F / 7D9E) SR645 V3 (7D9D / 7D9C) SR665 V3 (7D9B / 7D9A) SR630 V3 (7D72 / 7D73) SR650 V3 (7D75 / 7D76) SR850 V3 (7D97 / 7D96) SR860 V3 (7D94 / 7D93) SR630 V2 (7Z70 / 7Z71) SR650 V2 (7Z72 / 7Z73) SR670 V2 (7Z22 / 7Z23) SR635 (7Y98 / 7Y99) SR655 (7Y00 / 7Z01) SR645 (7D2Y / 7D2X) SR665 (7D2W / 7D2V) SR850 V2 (7D31 / 7D32) SR860 V2 (7Z59 / 7Z60)
Host interface *	PCI Express		
Interface *	Fiber		
Fiber ports quantity	2		
Fiber optic connector	SFP28		
PCI version	4.0		
Network			
Maximum data transfer rate *	25000 Mbit/s		
Design		System requirements	
Component for *	Server	Compatible operating systems	VMware vSphere Hypervisor (ESXi) 6.7 U3 VMware vSphere Hypervisor (ESXi) 7.0 VMware vSphere Hypervisor (ESXi) 7.0 U1 VMware vSphere Hypervisor (ESXi) 7.0 U2 VMware vSphere Hypervisor (ESXi) 7.0 U3 VMware vSphere Hypervisor (ESXi) 8.0
Product colour	Black, Green, Stainless steel		
Internal *	✔		
Operational conditions			
Operating temperature (T-T)		0 - 55 °C	
Storage temperature (T-T)		-40 - 65 °C	
Operating relative humidity (H-H)		5 - 95%	
Weight & dimensions			
Width		167 mm	
Height		63 mm	



0889488497300



889488497300

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.