

Epson ET-4750 Inkjet A4 4800 x 1200 DPI 33 ppm Wi-Fi

Brand : Epson

Product code: C11CG19401A2

Product name : ET-4750

- Ultra-low-cost per page: Reduce ink costs by 90%
 - Thousands of pages' worth of ink: Print up to 14,000 pages in black and 11,200 pages in colour
 - Next generation ink filling system: Enjoy hassle and mess-free refills with the enhanced ink bottles
 - Mobile printing and connectivity: Wi-Fi, Wi-Fi Direct, Ethernet & free mobile printing apps
 - Designed for business: 250 sheet front tray, fax, 30 page ADF and double-sided printing
- ET-4750, PrecisionCore, 4800x1200 dpi, 8/15 15 pages/Min, A4, 33.6 kbit/s, AC 100-240 V, 50-60 Hz, 375x347x231 mm, 2 Year Unlimited Printing Card

Epson ET-4750. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 4800 x 1200 DPI, Print speed (colour, normal quality, A4/US Letter): 20 ppm. Copying: Colour copying. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI. Faxing: Colour faxing. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: Black



Printing		Paper handling	
Duplex printing mode	Auto	Paper tray media types *	Envelopes, Plain paper
Print technology *	Inkjet	Multi-purpose tray media types	Legal, Letter
Printing *	Colour printing	ISO A-series sizes (A0...A9) *	A4, A5, A6
Duplex printing *	✓	ISO B-series sizes (B0...B9)	B5
Maximum resolution *	4800 x 1200 DPI	ISO C-series sizes (C0...C9)	C6
Print speed (black, normal quality, A4/US Letter) *	33 ppm	Envelopes sizes	10, C6, DL
Print speed (colour, normal quality, A4/US Letter)	20 ppm	Photo paper sizes	9x13,10x15,13x18,13x20,20x25
Print speed (ISO/IEC 24734) mono	15 ipm	Paper tray media weight	64 - 300 g/m ²
Print speed (ISO/IEC 24734) colour	8 ipm	Ports & interfaces	
Duplex print speed (ISO/IEC 24734) mono	6.5 ipm	Direct printing *	✓
Duplex print speed (ISO/IEC 24734) colour	4.5 ipm	USB port	✓
Time to first page (black, normal)	9 s	Network	
Time to first page (colour, normal)	15 s	Wi-Fi *	✓
Print margin top (min)	0 mm	Ethernet LAN *	✓
Print margin bottom (min)	0 mm	Security algorithms	64-bit WEP, 128-bit WEP, WPA-AES, WPA-PSK, WPA-TKIP
Print margin left (min)	0 mm	Mobile printing technologies	Apple AirPrint, Epson Connect, Epson Remote Print, Epson iPrint, Google Cloud Print
Print margin right (min)	0 mm	Performance	
Print margins (top, bottom, right, left)	3 mm	Card reader integrated	✗
Copying		Design	
Copying *	Colour copying	Product colour *	Black
Scanning		Market positioning *	Home & office
Scanning *	Colour scanning	Built-in display *	✓
Optical scanning resolution *	1200 x 2400 DPI	Display	LCD
Scan technology	CIS	Display diagonal	6.1 cm (2.4")
Fax		Touchscreen	✓
Faxing *	Colour faxing	Control type	Touch
Fax transmission speed	3 sec/page	Power	
Modem speed	33.6 Kbit/s	Power consumption (copying)	12 W
Fax memory	100 pages		

Fax		Power	
Auto-redialing	✓	Power consumption (ready)	5.4 W
Speed dialling	✓	Power consumption (sleep)	1 W
Fax speed dialing (max numbers)	60	Power consumption (off)	0.3 W
Fax delayed sending	✓	Energy Star Typical Electricity Consumption (TEC)	0.2 kWh/week
Error Correction Mode (ECM)	✓	AC input voltage	100 - 240 V
Features		AC input frequency	50 - 60 Hz
Printing colours *	Black, Cyan, Magenta, Yellow	System requirements	
Input & output capacity		Windows operating systems supported	Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP
Total number of input trays *	1	Mac operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Total input capacity *	250 sheets		
Paper input type	Paper tray		
Auto document feeder (ADF)	✓		
Auto document feeder (ADF) input capacity	30 sheets		
Paper handling		Weight & dimensions	
Maximum ISO A-series paper size *	A4	Width	375 mm
		Depth	347 mm
		Height	231 mm
		Weight	6.8 kg
Packaging content			
Cartridge(s) included			✓
Included cartridge capacity (black)			14000 pages
Included cartridge capacity (CMY)			11200 pages
Power cord included			✓
Warranty card			✓
Quick installation guide			✓
Other features			
Software CD			✓



8715946677125

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.