



Canon PG-560 / CL-561 ink cartridge 2 pc(s) Original Standard Yield Black, Cyan, Magenta, Yellow

Brand : Canon Product code: 3713C005

Product name : PG-560 / CL-561

- Spend less, print more
 - Print up to 180 colour, and 180 black & white A4 documents
 - 1x colour and 1x black ink cartridge
- PG-560 Black and CL-561 Colour Ink Cartridge Multi Pack

Canon PG-560 / CL-561 ink cartridge 2 pc(s) Original Standard Yield Black, Cyan, Magenta, Yellow:

This two-cartridge multipack contains 1x 8.3 ml colour, and 1x 7.5 ml black ink cartridge for printing vibrant colour documents and photo printouts. Designed for long-lasting results, each cartridge allows you to print up to 180 pages of A4 documents.

Produce rich, vivid and clear photos and documents
Print up to 180 pages of A4 documents with each cartridge
Rely on consistent quality and reliability from genuine Canon ink
Do your bit for the environment by returning every used ink cartridge to be re-used or recycled

Features		Features	
Black ink type	Pigment-based ink	Black ink page yield *	180 pages
Compatibility *	PIXMA TS5350 PIXMA TS5351 PIXMA TS5352	Colour ink page yield *	180 pages
Quantity per pack *	2 pc(s)	Type *	Original
Black ink cartridges quantity	1	Cartridge capacity	Standard Yield
Colour ink cartridges quantity	1	Printing colours *	Black, Cyan, Magenta, Yellow
Black ink volume	7.5 ml	Brand compatibility *	Canon
Colour ink volume	8.3 ml	Supply type *	Multi pack
		Cartridge return & recycling	✓
Logistics data			
		Harmonized System (HS) code	84439990



8714574662923

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.