

ASUS VT168HR computer monitor 39.6 cm (15.6") 1366 x 768 pixels WXGA LED Touchscreen Black

Brand : ASUS

Product code: 90LM02G1-B04170

Product name : VT168HR

- 15.6" 10-point touch capacity, suitable for any application that involves virtual keyboard or multi-touch
- -5 ° ~30 ° tilt angle, flexible enough for scenarios as a extend monitor or POS machine
- Slim Elegant Design with VESA mount (75mm x 75mm)
- Windows 10 compliance test passed device
- ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience.

15.6", 1366x768, TN, LED, PCAP, HDCP, HDMI, VGA, USB B, 377.8 x 280.7 x 189.4 mm

ASUS VT168HR. Display diagonal: 39.6 cm (15.6"), Display resolution: 1366 x 768 pixels, HD type:

WXGA, Display technology: LED, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 90°, Viewing angle, vertical: 60°. Built-in USB hub. VESA mounting. Product colour: Black



Display		Ergonomics	
Display diagonal *	39.6 cm (15.6")	Panel mounting interface	75 x 75 mm
Display resolution *	1366 x 768 pixels	Wall mountable	✓
HD type *	WXGA	Cable lock slot *	✓
Native aspect ratio *	16:9	Cable lock slot type	Kensington
Display technology *	LED	Height adjustment *	✗
Panel type *	TN	Tilt adjustment	✓
LED backlight	✓	Tilt angle range	-5 - 30°
Touchscreen *	✓		
Touchscreen technology	Projected capacitive system	Power	
Touch technology	Multi-touch	Energy efficiency class (SDR) *	B
Display brightness	220 cd/m²	Energy consumption (SDR) per 1000 hours *	6 kWh
Response time *	5 ms	Power consumption (typical) *	8 W
Anti-glare screen	✓	Power consumption (standby) *	0.5 W
Screen shape *	Flat	Power consumption (off)	0.5 W
Contrast ratio (typical) *	400:1	AC input voltage	100 - 240 V
Contrast ratio (dynamic)	100000000:1	AC input frequency	50 - 60 Hz
Maximum refresh rate *	60 Hz	Energy efficiency scale	A to G
Viewing angle, horizontal	90°	Weight & dimensions	
Viewing angle, vertical	60°	Width (with stand)	377.8 mm
Display number of colours *	262144 colours	Depth (with stand)	189.4 mm
Pixel pitch	0.252 x 0.252 mm	Height (with stand)	280.7 mm
Performance		Weight (with stand)	1.51 kg
NVIDIA G-SYNC *	✗	Width (without stand)	377.8 mm
AMD FreeSync *	✗	Depth (without stand)	44 mm
Multimedia		Height (without stand)	235.9 mm
Built-in microphone	✗	Packaging data	
Built-in camera *	✗	Package width	433.8 mm

Design		Packaging data	
Product colour *	Black	Package depth	122 mm
Ports & interfaces		Package height	349.7 mm
Built-in USB hub *	✓	Package weight	2.93 kg
VGA (D-Sub) ports quantity	1	Packaging content	
HDMI *	✓	Stand included	✓
HDMI ports quantity	1	Cables included	AC, HDMI, USB Type-A to USB Type-B, VGA
HDMI version	1.4	Other features	
HDCP	✓	Display viewable area (HxV)	344.23 x 193.54 mm
Ergonomics		Logistics data	
VESA mounting *	✓	Harmonized System (HS) code	85285210



4711081368403



4711081388258

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.