

Philips B Line 222B1TC/00 computer monitor 54.6 cm (21.5") 1920 x 1080 pixels Full HD LED Touchscreen Black

Brand : Philips

Product family: B Line

Product code: 222B1TC/00

Product name : 222B1TC/00

222B1TC LCD monitor with SmoothTouch

Philips B Line 222B1TC/00 computer monitor 54.6 cm (21.5") 1920 x 1080 pixels Full HD LED Touchscreen Black:

A durable, anti-glare touchscreen for flexible use, with articulating stand to angle as you need. Advanced In-Cell Touch (AIT) offers a slimmer look, superior touch sensitivity for quick response, outstanding and clearer visibility.

Philips B Line 222B1TC/00. Display diagonal: 54.6 cm (21.5"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub. VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	54.6 cm (21.5")	Cable lock slot type	Kensington
Display resolution *	1920 x 1080 pixels	Height adjustment *	✓
HD type *	Full HD	Adjustable height (max)	8.5 cm
Native aspect ratio *	16:9	Tilt adjustment	✓
Display technology *	LED	Tilt angle range	-5 - 90°
Panel type *	IPS	On Screen Display (OSD)	✓
Backlight type	W-LED	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Touchscreen *	✓		
Touchscreen technology	Capacitive		
Touch technology	Multi-touch	Number of OSD languages	21
Number of simultaneous touchpoints	10	Palm rejection area	30 x 30 mm
Display brightness (typical)	250 cd/m²	Plug and Play	✓
Display brightness	250 cd/m²	LED indicators	Operation, Stand-by
Response time *	4 ms	Power	
Screen shape *	Flat	Energy efficiency class (SDR) *	E
Aspect ratio	16:9	Energy consumption (SDR) per 1000 hours *	16 kWh
Contrast ratio (typical) *	1000:1	Power consumption (typical) *	13.1 W
Contrast ratio (dynamic)	50000000:1	Power consumption (standby) *	0.3 W
Dynamic contrast ratio marketing name	SmartContrast	Power consumption (off)	0 W
Maximum refresh rate *	75 Hz	Power consumption (PowerSave)	10.5 W
Viewing angle, horizontal	178°	AC input voltage	100 - 240 V
Viewing angle, vertical	178°	AC input frequency	50 - 60 Hz
Display number of colours *	16.7 million colours	Power supply type	Internal
Pixel pitch	0.24795 x 0.24795 mm	Energy efficiency scale	A to G
Pixel density	102 ppi		
Horizontal scan range	30 - 85 kHz		
Vertical scan range	48 - 60 Hz		
Viewable size, horizontal	47.6 cm		

Display		Operational conditions	
Viewable size, vertical	26.8 cm	Operating temperature (T-T)	0 - 40 °C
Display diagonal (metric)	54.6 cm	Storage temperature (T-T)	-20 - 60 °C
DDC/CI	✓	Operating relative humidity (H-H)	20 - 80%
Surface hardness	3H	Operating altitude	0 - 3658 m
sRGB coverage (typical)	102%	Non-operating altitude	0 - 12192 m
NTSC coverage (typical)	85%	Weight & dimensions	
Adobe RGB coverage	84%	Width (with stand)	489 mm
Display sRGB	✓	Depth (with stand)	227 mm
Performance		Height (with stand)	384 mm
NVIDIA G-SYNC *	✗	Weight (with stand)	6.13 kg
AMD FreeSync *	✗	Width (without stand)	489 mm
Component video sync	Separate Sync, Sync-on-green (SOG)	Depth (without stand)	52 mm
Flicker-free technology	✓	Height (without stand)	294 mm
Low Blue Light technology	✓	Weight (without stand)	2.79 kg
Operating system installed	Windows 10	Packaging data	
Windows operating systems supported	Windows 10	Package width	585 mm
Multimedia		Package depth	138 mm
Number of speakers	2	Package height	400 mm
RMS rated power	2 W	Package weight	8.27 kg
Built-in speaker(s) *	✓	Packaging content	
Built-in camera *	✗	Stand included	✓
Design		Cables included	HDMI, DisplayPort, USB Type-A to USB Type-B, AC
Product colour *	Black	Manual	✓
Front bezel colour	Black	Bundled software	SmartControl
Feet colour	Black	Sustainability	
Ports & interfaces		Sustainability certificates	ENERGY STAR, TCO
Built-in USB hub *	✓	Doesn't contain	PVC/BFR, Mercury
Number of upstream ports	1	Other features	
USB Touch port	✓	Display viewable area (HxV)	476.06 x 267.79 mm
VGA (D-Sub) ports quantity	1	Picture enhancement	SmartImage
HDMI *	✓	Regulatory Approvals	CB; SEMKO; TUV/GS; TUV Ergo; CU-EAC; EAEU RoHS; CE Mark; ICES-003; FCC Class B; TUV Eye Comfort certified
HDMI ports quantity	1		Heavy metals free
HDMI version	1.4		Hg (mercury)
DisplayPorts quantity	1	Folding angle	70°
DisplayPort version	1.2	Touch method	Finger
Audio output	PC audio-in, HeadphoneY	EasyRead mode	✓
Headphone out *	✓	Compliance certificates	RoHS
PC Audio in	✓	Mean time between failures (MTBF)	70000 h
Ergonomics		Certification	CB, SEMKO, TUV/GS, TUV Ergo, CU-EAC, EAEU RoHS, CE Mark, ICES-003, FCC Class B, TUV Eye Comfort certified
VESA mounting *	✓		
Panel mounting interface	100 x 100 mm		
Wall mountable	✓	Recycling data	
Cable lock slot *	✓	Recyclable packaging material	100%
Logistics data			
		Harmonized System (HS) code	85285210



8712581776770

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.