

Epson Semigloss 200 White Semi-gloss

Brand : Epson

Product code: C13S450378

Product name : Semigloss 200



Production Photo Paper Semigloss 200 44" x 30m
Epson Semigloss 200. Finish type: Semi-gloss, Media weight: 200 g/m², Print technology: Inkjet. Roll width: 111.8 cm, Roll length: 30 m, Core diameter: 5.08 cm. Quantity per pack: 1 pc(s), Package width: 130 mm, Package depth: 1165 mm. Country of origin: Germany

Features		Features	
Print technology	Inkjet	Compatible products	SureColor SC-T7200 (with Stand)
Product colour	White		SureColor SC-T5400M-MFP
Finish type *	Semi-gloss		SureColor SC-T5400 SureColor SC-T5200 SureColor SC-T5100 Series
Media weight *	200 g/m²		SureColor SC-T3400 Series
Best uses	Photo, CAD, Production		SureColor SC-T3200 (with stand)
Tint (L*a*b)	L* = 94 a* = 2 b* = -7.5 M0 (UV)		SureColor SC-T3100 Series
Paper brightness	2470		SureColor SC-P9500 SureColor SC-P9000V SureColor SC-P9000 Violet Spectro SureColor SC-P9000 Series
Printing media thickness	190 µm		SureColor SC-P9000 STD Spectro SureColor SC-P8000 Series SureColor SC-P8000 STD Spectro SureColor SC-P8000 STD SureColor SC-P7500 Spectro SureColor SC-P7500
Printing media gloss level	95		SureColor SC-P7000V SureColor SC-P7000 Violet Spectro SureColor SC-P7000 Series SureColor SC-P7000 STD Spectro SureColor SC-P6000 Series SureColor SC-P6000 STD Spectro SureColor SC-P6000 STD SureColor SC-P20000 SureColor SC-P10000 Epson Stylus Pro 9900 Epson Stylus Pro 9890
Operational conditions			
Operating temperature (T-T)	15 - 25 °C		
Operating relative humidity (H-H)	35 - 65%		
Weight & dimensions			
Roll width	111.8 cm		
Roll length	30 m		
Core diameter	5.08 cm		
Packaging data			
Quantity per pack	1 pc(s)		
Package width	130 mm		
Package depth	1165 mm		
Package height	120 mm		
Package weight	8 kg		
Logistics data			
Harmonized System (HS) code	37032000		
Other features			
Country of origin	Germany		



8715946686912

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.