



Lenovo 4X41A30365 laptop case 39.6 cm (15.6") Toploader bag Black

Brand : Lenovo

Product code: 4X41A30365

Product name : 4X41A30365

- Eco-friendly: 100% recycled exterior, equivalent to over 8 plastic bottles
 - Dedicated, separate laptop compartment
 - Large storage area for documents and power adapters
 - Front zip pocket keeps smaller accessories organized
 - Front quick-stash pocket for mobile phone or passport
 - Easy-grip zippers, comfortable carry handle, and luggage strap
- 15.6" max, Black, 513 g, 417 x 78 x 360 mm

Lenovo 4X41A30365 laptop case 39.6 cm (15.6") Toploader bag Black:

With the perfect blend of professionalism and athleticism, the ThinkPad Essential Plus 15.6" Topload can take you from the office or campus, and beyond. Spacious compartments keep your devices and essentials secure, organized, and accessible, while ballistic nylon and rugged hardware protect against weather and daily wear.

Lenovo 4X41A30365. Case type: Toploader bag, Maximum screen size: 39.6 cm (15.6"), Carrying handle(s), Shoulder strap. Weight: 513 g. Surface coloration: Monochromatic



Features		Features	
Surface coloration	Monochromatic	Quantity	1
Maximum screen size *	39.6 cm (15.6")	Weight & dimensions	
Case type *	Toploader bag	Width	417 mm
Product main colour *	Black	Depth	78 mm
Brand compatibility *	Any brand	Height	360 mm
Front pocket	✓	Weight	513 g
Carrying handle(s)	✓	Notebook compartment dimensions (W x D x H)	381 x 262 x 34 mm
Shoulder strap	✓	Package width	430 mm
Removable shoulder strap	✓	Package depth	60 mm
Made with recycled materials	✓	Package height	360 mm
Recycled materials used for making	Polyethylene terephthalate (PET)	Package weight	726 g
Total amount of recycled materials used for making	100%	Package type	Polybag
Closure type	Zipper	Logistics data	
		Harmonized System (HS) code	84733080



0195235991183



195235991183

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.