

ASUS ProArt PA247CV computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD Black, Silver

Brand : ASUS

Product family: ProArt

Product code: 90LM03Y1-B02370

Product name : PA247CV

- 23.8-inch Full HD (1920 x 1080) LED backlight display with IPS 178° wide viewing angle panel
 - International color standard 100% sRGB and 100% Rec. 709 wide color gamut
 - Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
 - Extensive connectivity including DP over USB-C™ with 65W Power Delivery, DisplayPort, HDMI, USB hub
 - 75Hz refresh rate and Adaptive-Sync technology (48~75Hz) to animated content with fast action and eliminate screen tearing
 - Daisy-chaining allows users to daisy chain up to four monitors for a multi-display workstation via DisplayPort
 - Ergonomic design with +35° ~ -5° tilt, ±90° swivel, ±90° pivot and 130mm height adjustments for a comfortable viewing experience
- ProArt Display PA247CV



ASUS ProArt PA247CV computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD Black, Silver:

ASUS ProArt Display PA247CV Professional Monitor – 23.8-inch, IPS, Full HD (1920 x 1080), 100% sRGB, 100% Rec. 709, Colour Accuracy ΔE < 2, Calman Verified, USB-C, DisplayPort Daisy-chaining, ProArt Preset, ProArt Palette, Ergonomic Stand

Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	USB Power Delivery up to	65 W
Display resolution *	1920 x 1080 pixels	HDMI *	✓
HD type *	Full HD	HDMI ports quantity	1
Native aspect ratio *	16:9	HDMI version	1.4
Panel type *	IPS	DisplayPorts quantity	2
Touchscreen *	✗	DisplayPort version	1.2
Display brightness (typical)	300 cd/m²	Headphone out *	✓
Response time *	5 ms	Headphone outputs	1
Display surface	Matt	Headphone connectivity	3.5 mm
Screen shape *	Flat	HDCP	✓
Contrast ratio (typical) *	1000:1	DC-in jack	✓
Contrast ratio (dynamic)	100000000:1		
Dynamic contrast ratio marketing name	ASUS Smart Contrast Ratio (ASCR)		
Maximum refresh rate *	75 Hz		
Viewing angle, horizontal	178°		
Viewing angle, vertical	178°		
Display number of colours *	16.7 million colours		
Pixel pitch	0.2745 x 0.2745 mm		
Viewable size, horizontal	52.7 cm		
Viewable size, vertical	29.6 cm		
Digital horizontal frequency	30 - 83 kHz		
Digital vertical frequency	48 - 75 Hz		
sRGB coverage (typical)	100%		
Performance		Ergonomics	
NVIDIA G-SYNC *	✗	VESA mounting *	✓
AMD FreeSync *	✗	Panel mounting interface	100 x 100 mm
Flicker-free technology	✓	Cable lock slot *	✓
Low Blue Light technology	✓	Cable lock slot type	Kensington
		Height adjustment *	✓
		Adjustable height (max)	13 cm
		Pivot	✓
		Pivot angle	90 - -90°
		Swivelling	✓
		Swivel angle range	90 - -90°
		Tilt adjustment	✓
		Tilt angle range	35 - -5°
		Power	
		Energy efficiency class (SDR) *	D
		Energy consumption (SDR) per 1000 hours *	15 kWh

Multimedia		Power	
Number of speakers	2	Power consumption (typical) *	18 W
RMS rated power	4 W	Power consumption (PowerSave)	0.5 W
Built-in speaker(s) *	✓	AC input voltage	100 - 240 V
Built-in camera *	✗	Energy efficiency scale	A to G
Design		Weight & dimensions	
Market positioning *	Graphics design	Width (with stand)	539.7 mm
Product colour *	Black, Silver	Depth (with stand)	211.4 mm
Feet colour	Silver	Height (with stand)	471.8 mm
Ports & interfaces		Weight (with stand)	6.3 kg
Built-in USB hub *	✓	Width (without stand)	539.7 mm
USB hub version	2.0 / 3.2 Gen 1 (3.1 Gen 1)	Depth (without stand)	52.8 mm
USB upstream port type	USB Type-C	Height (without stand)	329.9 mm
Number of upstream ports	1	Weight (without stand)	4.2 kg
Number of USB Type-C upstream ports quantity	1	Packaging data	
USB Type-A downstream ports quantity	4	Package width	632 mm
		Package depth	216 mm
		Package height	450 mm
		Package weight	8.3 kg



4718017886864

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.