

## dbramante1928 New York - iPhone 13 Pro - Night Black

**Brand :** dbramante1928

**Product code:** NY61PBBL5520

**Product name :** New York - iPhone 13 Pro - Night Black

New York - iPhone 13 Pro - Night Black

[dbramante1928 New York - iPhone 13 Pro - Night Black:](#)

This 2-in-1 wallet case, with its exceptional functionality, has been beautifully designed for use either as an ultra-slim impact protective case or a feature-rich stylish wallet, or both. Designed in Denmark by a Climate Positive Company, protect your device and the planet with this feature-rich, eco-friendly 2-in-1 wallet case.

With its impact protective 'snap-in place' detachable cradle, New York is fashioned from the same iconic Pebbled full-grain leathers invented by Prada and used by many high-end fashion houses. Perfect for those looking to bring effortless style, protection and organisation to their everyday lives.  
dbramante1928 New York - iPhone 13 Pro - Night Black. Case type: Wallet case, Brand compatibility: Apple, Compatibility: iPhone 13 Pro, Maximum screen size: 15.5 cm (6.1"), Surface coloration: Monochromatic, Product colour: Black, Number of card pockets: 3



| Features                  |                   | Packaging data                             |                          |
|---------------------------|-------------------|--------------------------------------------|--------------------------|
| Maximum screen size *     | 15.5 cm (6.1")    | Package depth                              | 25 mm                    |
| Surface coloration        | Monochromatic     | Package height                             | 207 mm                   |
| Compatibility *           | iPhone 13 Pro     | Package weight                             | 155 g                    |
| Case type *               | Wallet case       | Logistics data                             |                          |
| Product colour *          | Black             | Harmonized System (HS) code                | 85177900                 |
| Brand compatibility *     | Apple             | Country of origin                          | India                    |
| Closure type              | Magnetic closure  | Shipping (inner) case net weight           | 59 g                     |
| Card pocket               | ✓                 | Shipping (inner) case gross weight         | 86 g                     |
| Number of card pockets    | 3                 | Quantity outer carton                      | 30 pc(s)                 |
| Protection features       | Scratch resistant | Master (outer) case width                  | 395 mm                   |
| Easy to apply             | ✓                 | Master (outer) case length                 | 245 mm                   |
| Weight & dimensions       |                   | Master (outer) case height                 | 230 mm                   |
| Width                     | 76 mm             | Master (outer) case net weight             | 740 g                    |
| Depth                     | 21 mm             | Master (outer) case gross weight           | 740 g                    |
| Height                    | 150 mm            | Master (outer) case volume                 | 22258.25 cm <sup>3</sup> |
| Weight                    | 96 g              | Master (outer) cases per pallet layer (EU) | 48 pc(s)                 |
| Packaging content         |                   | Products per pallet (EU)                   | 1440 pc(s)               |
| Quantity per pack         | 30 pc(s)          | Pallet gross weight                        | 3.71 kg                  |
| Sustainability            |                   |                                            |                          |
| Sustainability compliance | ✓                 |                                            |                          |
| Packaging data            |                   |                                            |                          |
| Package width             | 117 mm            |                                            |                          |



5711428055200

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.