



APC Base Enclosure Config (Contained 42U Easy Rack, SRVPM6K, PDP, Energy Meter, Local Management, EFC, Lighting)

Brand : APC

Product code: EMDC42U6KP2

Product name : Base Enclosure Config (Contained 42U Easy Rack, SRVPM6K, PDP, Energy Meter, Local Management, EFC, Lighting)


- Base Enclosure Config (Contained 42U Easy Rack, SRVPM6K, PDP, Energy Meter, Local Management, EFC, Lighting)
 - Pre-configured Micro Data Center platform designed to address essential needs of distributed IT application in a variety of commercial environments.
- Base Enclosure Config (Contained 42U Easy Rack, SRVPM6K, PDP, Energy Meter, Local Management, EFC, Lighting)

APC Base Enclosure Config (Contained 42U Easy Rack, SRVPM6K, PDP, Energy Meter, Local Management, EFC, Lighting):

Configured 42U solution with pre-integrated power distribution panel, monitoring device, sensors, emergency fan, LED lighting and UPS Power Module. Fully enabled for EcoStruxure remote management connectivity. Made for indoor commercial environments. Compact design to easily roll with recessed casters and levelling feet. Protect equipment from environment and physical security threats. Quickly deploy IT gear and connectivity to enable digitalization.

Features		Weight & dimensions	
Rack capacity *	42U	Depth	1200 mm
Type *	Freestanding rack	Height	2020 mm
Maximum weight capacity *	1200 kg	Weight	198 kg
Maximum weight capacity (rolling)	600 kg	Packaging data	
Product colour	Black	Package width	800 mm
Weight & dimensions		Package depth	1400 mm
Width	600 mm	Package height	2180 mm
		Logistics data	
		Harmonized System (HS) code	85381000





0731304432173



731304432173



4064575389447

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.