

StarTech.com RH2A-10M-HDMI-CABLE HDMI cable HDMI Type A (Standard) Black

Brand : StarTech.com

Product code: RH2A-10M-HDMI-CABLE

Product name : RH2A-10M-HDMI-CABLE

StarTech.com 30ft (9.1m) Active HDMI Cable w/ Ethernet - HDMI 2.0 4K 60Hz UHD - Rugged HDMI Cord w/ Aramid Fiber - Durable High Speed HDMI Cable - Heavy-Duty HDMI 2.0 Cable
StarTech.com RH2A-10M-HDMI-CABLE. Cable length: 10 m, Connector 1: HDMI Type A (Standard), Connector 1 gender: Male, Connector 2: HDMI Type A (Standard), Connector 2 gender: Male, Connector contacts plating: Gold, HDMI version: 2.0, Audio Return Channel (ARC), Product colour: Black



Features	
Cable length *	10 m
Connector 1 *	HDMI Type A (Standard)
Connector 2 *	HDMI Type A (Standard)
Connector 1 gender *	Male
Connector 2 gender *	Male
Connector 1 form factor	Straight
Connector 2 form factor	Straight
Product colour *	Black
HDMI version	2.0
Dolby technologies	Dolby TrueHD, Dolby Atmos, Dolby Digital Plus
Audio Return Channel (ARC)	✓
HDMI Ethernet channel	✓
HDCP	✓
HDCP version	2.2
High Dynamic Range (HDR) supported	✓
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)
Supported digital audio channels (uncompressed)	32
AWG wire size	28
Connector contacts plating *	Gold
Cable material	Copper
Cable type	Round cable

Features	
Cable jacket material	Thermoplastic elastomer (TPE)
Operational conditions	
Operating temperature (T-T)	0 - 50 °C
Storage temperature (T-T)	0 - 50 °C
Operating relative humidity (H-H)	0 - 85%
Sustainability	
Sustainability compliance	✓
Certificates	
Compliance certificates	RoHS, CE
Weight & dimensions	
Cable diameter	7.5 mm
Weight	700 g
Packaging data	
Package width	330 mm
Package depth	252 mm
Package height	120 mm
Package weight	700 g
Quantity per pack *	1 pc(s)
Logistics data	
Master (outer) case width	430 mm
Master (outer) case length	380 mm
Master (outer) case height	290 mm
Products per master (outer) case	16 pc(s)



0065030895828



065030895828

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.