

Targus DOCK710EUZ laptop dock/port replicator USB 3.2 Gen 2 (3.1 Gen 2) Type-C Black

Brand : Targus

Product code: DOCK710EUZ

Product name : DOCK710EUZ

- Unique hybrid solution for Universal (DisplayLink®) and DP Alt Mode host compatibility
 - Supports a single 8K monitor @ 30 Hz or up to four 4K UHD @ 60 Hz monitors via two HDMI and two DisplayPort™ ports
 - Power Delivery 3.0 up to 100 W for USB-C® hosts
 - 1x USB 3.2 Gen 2 Type-C (10 Gbps) port
 - 1x USB 3.2 Gen 2 Type-A (10 Gbps) ports (fast charging) and 3x USB 3.2 Gen 1 Type-A (5 Gbps) ports
 - 1x Gigabit Ethernet port
 - 1 x 3.5 mm combo audio jack for mics, speakers, and earphones
 - Integrated lock slot compatible with Targus® ASP9 series universal locks to safeguard equipment
 - 1 m USB-C (10 Gbps) detachable host cable tethered adapter for host devices with USB-A ports only
 - Compatible with Targus VESA® Mounting Bracket (ACX003GLZ, sold separately)
- USB 3.2 Gen 2 Type-C host interface, Power Delivery 3.0, 12 ports



Ports & interfaces		Performance	
Host interface *	USB 3.2 Gen 2 (3.1 Gen 2) Type-C	Cable lock slot type	Kensington
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	3	Product colour *	Black
USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity	1	Hub interfaces	3.5mm, DisplayPort, HDMI, RJ-45, USB 3.2 Gen 1 (3.1 Gen 1) Type-A, USB 3.2 Gen 2 (3.1 Gen 2) Type-A, USB 3.2 Gen 2 (3.1 Gen 2) Type-C
USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity	1	Country of origin	Taiwan
USB Power Delivery (USB PD)	✓	Power	
USB Power Delivery revision	3.0	Power supply type	AC
USB Power Delivery up to	100 W	Software	
HDMI ports quantity *	2	Windows operating systems supported	✓
DisplayPorts quantity	2	Mac operating systems supported	✓
Combo headphone/mic port	✓	Weight & dimensions	
DC-in jack	✓	Width	180 mm
USB Type-C DisplayPort Alternate Mode	✓	Depth	250 mm
Network		Height	90 mm
Ethernet LAN (RJ-45) ports	1	Weight	1.36 kg
Performance		Packaging data	
Maximum refresh rate	60 Hz	Quantity per pack	1 pc(s)
		Packaging content	
		AC adapter included	✓
		Quick start guide	✓



5051794036848



5051794040319

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.