

Allied Telesis AT-VST-APL-06-60 network management device Ethernet LAN

Brand : Allied Telesis

Product code: AT-VST-APL-06-60

Product name : AT-VST-APL-06-60

AT-Vista Manager Network Appliance with 6 x 10/100/1000T copper ports and a single fixed power supply (19 inch rack-mount brackets and four regional AC power cords included)

Allied Telesis AT-VST-APL-06-60 network management device Ethernet LAN:

The Vista Manager Network Appliance (VST-APL) delivers state-of-the-art network automation, with integrated monitoring and management. Combining powerful applications for automating network management and security, and providing visibility with actionable reporting, reduces administration effort, complexity and cost.

Allied Telesis AT-VST-APL-06-60. Number of users: 5000 user(s). Ethernet LAN data rates: 10,100,1000 Mbit/s, Cabling technology: 10/100/1000. Product colour: Grey. Weight: 4.5 kg, Width: 438 mm, Depth: 292 mm. Cables included: AC

Performance		Power	
Number of Remote Access Points (max) *	60	Power over Ethernet (PoE) *	✗
Number of users *	5000 user(s)	Design	
Network		Rack mounting	✓
Ethernet LAN	✓	Product colour	Grey
Ethernet LAN data rates	10,100,1000 Mbit/s	Weight & dimensions	
Cabling technology	10/100/1000	Weight	4.5 kg
Management features		Width	438 mm
Web-based management	✓	Depth	292 mm
Ports & interfaces		Height	44 mm
Ethernet LAN (RJ-45) ports	6	Packaging content	
Power		Cables included	AC
Number of power supply units	1	Packaging data	
		Package weight	7.5 kg



0767035219462



767035219462

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.