



APC NetShelter Switched Rack PDU, 0U, 5.0kW, 200V and 208V, 30A, 21 C13/C15 and 3 C19/C21 outlets

Brand : APC

Product code: APDU9941

Product name : APC NetShelter Switched Rack PDU, 0U, 5.0kW, 200V and 208V, 30A, 21 C13/C15 and 3 C19/C21 outlets

APC NetShelter Switched Rack PDU, 0U, 5.0kW, 200V and 208V, 30A, 21 C13/C15 and 3 C19/C21 outlets
APC NetShelter Switched Rack PDU, 0U, 5.0kW, 200V and 208V, 30A, 21 C13/C15 and 3 C19/C21 outlets.
PDU types: Switched, Rack capacity: 0U, Type: Single-phase. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C15 coupler, C19 coupler, C21 coupler, Power plug: NEMA L6-30P. Nominal input voltage: 90 - 264 V, Maximum current: 30 A, Nominal output voltage: 200 - 208 V. Compliance certificates: RoHS, Certification: CUL , FCC 15 A, ICES-003, PSE. Width: 55 mm, Depth: 46 mm, Height: 1829 mm



Design		Sustainability	
PDU types *	Switched	Sustainability compliance	✓
Type	Single-phase	Operational conditions	
Rack capacity *	0U	Operating temperature (T-T)	-5 - 60 °C
Mounting	Vertical	Storage temperature (T-T)	-25 - 65 °C
Product colour	Black	Operating relative humidity (H-H)	5 - 95%
Ports & interfaces		Operating altitude	0 - 3048 m
AC outlets quantity *	24 AC outlet(s)	Non-operating altitude	0 - 15240 m
Power plug	NEMA L6-30P	Weight & dimensions	
AC outlet types *	C13 coupler, C15 coupler, C19 coupler, C21 coupler	Width	55 mm
Ethernet LAN (RJ-45) ports	1	Depth	46 mm
Power		Height	1829 mm
Nominal input voltage *	90 - 264 V	Weight	8.5 kg
Maximum current *	30 A	Packaging content	
Nominal output voltage	200 - 208 V	Manual	✓
Load capacity	4992 VA	Packaging data	
Certificates		Package weight	10 kg
Compliance certificates	RoHS	Package width	165 mm
Certification	CUL , FCC 15 A, ICES-003, PSE	Package depth	124 mm
		Package height	2040 mm



0731304356264



731304356264

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.