

ASUS Hyper M.2 x16 Gen 4 interface cards/adaptor Internal

Brand : ASUS

Product code: 90MC08A0-M0EAY0

Product name : Hyper M.2 x16 Gen 4

- Two-phase power solution with up to 14-watt output supports the latest NVMe drives
 - Large heatsink and active fan reduces M.2 SSD temperatures for unthrottled transfer speeds and enhanced reliability
 - Adapted server-grade PCB supports up to four PCIe 4.0/3.0 M.2 drives, with up to 256 Gbps bandwidth for smooth data transfers
 - Compatible with AMD TRX40/X570 PCIe 4.0 for NVMe RAID and supports Intel® platform RAID-on-CPU functions
 - Also support other vendors' motherboards via PCIe bifurcation in BIOS setting
- PCIe 4.0/3.0 x16, Up to 4 x M.2, 1 x M.2 FAN Power Switch, 4 x M.2 access LEDs
ASUS Hyper M.2 x16 Gen 4. Host interface: PCIe, Output interface: M.2, Expansion card standard: PCIe 4.0. Product colour: Silver, Purpose: PC, Cooling type: Active. Data transfer rate (max): 256 Gbit/s. Width: 270 mm, Depth: 122 mm, Height: 15 mm. Package type: Box



Ports & interfaces		Design	
Host interface *	PCIe	Easy to install	✓
Output interface *	M.2	Features	
Expansion card standard	PCIe 4.0	Data transfer rate (max)	256 Gbit/s
Design		Weight & dimensions	
Internal *	✓	Width	270 mm
Product colour	Silver	Depth	122 mm
Purpose	PC	Height	15 mm
Cooling type	Active	Packaging data	
Number of fans	1 fan(s)	Quantity	1
Number of expansion slots	4	Package type	Box
LED indicators	Access	Logistics data	
		Harmonized System (HS) code	84733020



4718017624923

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.