

Philips SPK7307B/00 mouse Office Ambidextrous RF Wireless Optical 1600 DPI

Brand : Philips

Product code: SPK7307B/00

Product name : SPK7307B/00

- High-definition optical tracking for smooth control
 - Comfortable ergonomic mouse design feels great
 - Ambidextrous shape feels good in right or left hand
 - Buttons last millions of clicks for durability
 - Plug-and-play wireless for convenience
- 3000 series SPK7307B Wireless mouse



Philips SPK7307B/00 mouse Office Ambidextrous RF Wireless Optical 1600 DPI:

Take this mouse with you wherever you go. Ideal for fitting into your palm and a bag, this 2.4G wireless mouse has an optical sensor that makes control simple and firsthand.
Philips SPK7307B/00. Form factor: Ambidextrous. Movement detection technology: Optical, Device interface: RF Wireless, Movement resolution: 1600 DPI, Buttons type: Pressed buttons, Buttons quantity: 3, Scroll type: Wheel. Power source: Batteries. Product colour: Black

Mouse		Ergonomics	
Number of scroll wheels	1	Wireless range	15 m
Scrolling directions	Vertical	Power	
Purpose *	Office	Power source *	Batteries
Connectivity technology *	Wireless	System requirements	
Device interface *	RF Wireless	Windows operating systems supported	✓
Movement detection technology *	Optical	Mac operating systems supported	✓
Movement resolution *	1600 DPI	Linux operating systems supported	✓
Buttons type	Pressed buttons	Weight & dimensions	
Scroll type *	Wheel	Width	65 mm
Buttons quantity *	3	Depth	110 mm
Buttons durability (million clicks)	3	Height	35 mm
Frequency band	2.4 GHz	Weight	83 g
Design		Packaging data	
Form factor *	Ambidextrous	Quantity per pack *	1 pc(s)
Ergonomic design	✓	Technical details	
Product colour *	Black	Driver requirement	✗
Surface coloration	Monochromatic		



8712581778873

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.