

Brother BDL-7J000102-058 printer label White Non-adhesive printer label

Brand : Brother

Product code: BDL-7J000102-058

Product name : BDL-7J000102-058

- Receipt width: 101.6mm
- Roll length: 32.2m
- Direct thermal receipt printing
- High quality receipt print outs
- Compatible with selected RJ and TD printers

The BDL-7J000102-058 continuous receipt roll, measuring 101.6mm in width, has been Certified by Brother International Europe. Each purchase contains 20 rolls per order.

Brother BDL-7J000102-058 printer label White Non-adhesive printer label:

The Brother BDL-7J000102-058 continuous white receipt roll has been created to meet your receipt printing requirements. The 101.6mm receipt paper produces high-quality direct thermal print outs, perfect for delivery confirmations, quotes, estimates, tickets and fines.
Brother BDL-7J000102-058. Product colour: White, Label type: Non-adhesive printer label, Type: Continuous label. Label width: 10.2 cm, Dimensions (WxDxH): 58 x 58 x 100 mm, Weight: 4.78 kg. Package weight: 5 kg. Master (outer) cases per pallet: 63 pc(s), Layers per pallet: 9 pc(s), Products per pallet: 1260 pc(s). Country of origin: Spain



Features		Packaging content	
Product colour *	White	Rolls per pack	20
Label type	Non-adhesive printer label	Technical details	
Type	Continuous label	Master (outer) cases per pallet layer	7 pc(s)
Print technology	Direct thermal	Pallet type	800 x 1200 mm
Purpose	Receipt	Logistics data	
Shape	Rectangle	Master (outer) cases per pallet	63 pc(s)
Perforated	✗	Layers per pallet	9 pc(s)
Compatible products	Brother RJ, TD	Products per pallet	1260 pc(s)
Weight & dimensions		Pallet gross weight	339.3 kg
Label width	10.2 cm	Pallet gross height	13.2 cm
Dimensions (WxDxH)	58 x 58 x 100 mm	Harmonized System (HS) code	84439990
Weight	4.78 kg	Other features	
Packaging data		Country of origin	Spain
Package weight	5 kg		



5014047600814

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.