

Targus AWU100205GL laptop stand Silver 39.6 cm (15.6")

Brand : Targus

Product code: AWU100205GL

Product name : AWU100205GL

- Robust laptop stand with integrated USB hub, foldable to compact size (25.3 x 6 x 1.83 cm), ideal for modern hybrid workers travelling between locations
 - Made of high-quality aluminum with high heat reduction. Versatile and universal, supports most laptop devices from 10" - 15.6"
 - Expand your laptop USB-C port with one cable to 4x USB-A (3.2 Gen 1) ports
 - 4x USB-A support fast 5 Gbps data transfer, perfect for external flash drives
 - USB-A ports support max 1.5 A charging for your accessories or smart devices (4 USB-A ports share max 15W)
 - USB-C port under the stand offers neat power cable management and supports Power Delivery 3.0 with 100W power pass-through. Share 100W power between laptop devices via USB-C cable and other devices via USB-A and data ports
- Portable Stand with Integrated USB-A Hub



Design		Ports & interfaces	
Product type *	Laptop stand	USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	4
Product colour *	Silver	USB data transfer rates	5000 Mbit/s
Material	Aluminium	USB charging port	✓
Minimum notebook screen size compatibility	25.4 cm (10")	USB Power Delivery (USB PD)	✓
Maximum notebook screen size compatibility	39.6 cm (15.6")	USB Power Delivery revision	3.0
Number of devices supported	1	USB Power Delivery up to	100 W
Ergonomics		System requirements	
Foldable	✓	Windows operating systems supported	✓
Adjustable	✓	Mac compatibility	✓
Height adjustment	✓	Weight & dimensions	
Number of height positions	5	Width	62 mm
Number of adjustment positions	5	Depth	260 mm
Cable management	✓	Height	27 mm
Ports & interfaces		Weight	360 g
Built-in USB hub	✓	Packaging content	
Host interface	USB 3.2 Gen 1 (3.1 Gen 1) Type-C	Cables included	USB Type-C
		Technical details	
		Country of origin	China
		Logistics data	
		Harmonized System (HS) code	84733080



5051794036619



0092636357399



092636357399

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.